

## In-Sure™ Push-In Wire Connectors

- No-twist connection reduces repetitive motion fatigue
- Low insertion force for fast and easy connections
- Compact size makes installation easy
- Clear shell gives visual verification of connection
- UL Listed to 486C and CSA Certified to C22.2 #188
- UL 467 Listed for grounding and bonding applications

- Accepts the following copper wire sizes

### - Solid

#20 - #12 solid

### - Stranded

#16 - #14 (19 strand or less)

#18 (7 strand or less)

### - Stranded (Tin Bonded)

#14 - #12 (19 strand or less)

#16 (26 strand or less)


#18 (16 strand or less)



Model	Color	Ports	Length		Width		Height		Quantity	Cat. No.
			In.	mm	In.	mm	In.	mm		
84	Red	2	.355	9.02	.434	11.02	.729	18.52	Box of 100	<b>30-084</b>
									Jar of 300	<b>30-084J</b>
									Box of 1,000	<b>30-184</b>
									Box of 5,000	<b>30-684</b>
85	Orange	3	.355	9.02	.591	15.01	.729	18.52	Box of 100	<b>30-085</b>
									Jar of 250	<b>30-085J</b>
									Box of 1,000	<b>30-185</b>
									Box of 5,000	<b>30-685</b>
86	Yellow	4	.355	9.02	.748	18.99	.729	18.52	Box of 100	<b>30-086</b>
									Jar of 200	<b>30-086J</b>
									Box of 1,000	<b>30-186</b>
									Box of 4,000	<b>30-686</b>
87	Gray	5	.355	9.02	.907	23.03	.729	18.52	Box of 50	<b>30-087</b>
									Jar of 150	<b>30-087J</b>
									Box of 1,000	<b>30-187</b>
									Box of 5,000	<b>30-687</b>
88	Blue	6 Stacked	.607	15.42	.603	15.32	.729	18.52	Box of 50	<b>30-088</b>
									Jar of 100	<b>30-088J</b>
									Box of 1,000	<b>30-188</b>
									Box of 5,000	<b>30-688</b>
90	Black	8	.355	9.02	1.38	35.03	.717	18.21	Box of 50	<b>30-090</b>
									Jar of 100	<b>30-090J</b>
									Box of 1,000	<b>30-190</b>
									Box of 2,000	<b>30-690</b>

**Installation as easy  
as 1-2-3...**

### 1. Strip



### 2. Push



### 3. Connect



COPPER TO COPPER ONLY. Do not use on aluminum.

Temperature rating: 105°C (221°F) maximum

600V maximum building wire, 1000V maximum signs or lighting fixtures

