



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



3010 120V 1500W SPST Flush Mounting W/Plate

Nsi Industries

Catalog Number	3010
Manufacturer	Nsi Industries
Description	Flush Mount, 120 V Ac, 1500 W, 1 In Width, 2 In Height, Lexan Housing Material, SPST Switch Type, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Flush Mount, 0.3 LB/Ea
Weight per unit	0.3000 (lbs/each)
Product Category	Lighting Photocells

Features

indoor/outdoor	Outdoor
pallet quantity	1920
Power Source	Hardwired
supply voltage	120 Vac
Timing Range	2 Minutes

Dimensions and Weight

Size	3 in x 3 in x 5.625 in
------	------------------------

Descriptions

Description	120V 1500W SPST FLUSH MOUNTING W/PLATE
extra long description	PROG PTORK3010 PHOTO CONTROL WALL

Manufacturer Information

Brand	PROGRESS
GTIN	00786261600219
Manufacturers Part Number	PTORK3010
UPC	786261600219

Taxonomies, Classifications, and Categories

Category Description	SIGNALING EQUIPMENT
----------------------	---------------------

Packaging

Carton	1
Weight Per each	0.3

Uses, Certifications, and Standards

Frequency Rating	50-60 Hz
Mounting	Flush Mount
Operating Temperature standard	-40 to + 140 F cULus