



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



301032J In-Sure Push-In Conn, 32 2-Port Red, 300/Jar *Ideal*

Catalog Number	301032J
Manufacturer	Ideal
Description	Push-In Wire Connector, Red Insulation Color, +221 °F Operating Temperature, 0.780 In Overall Length, 0.520 In Overall Width, 0.380 In Overall Height, 600 V (Building Wire);1000 V (Maximum Signs/Lighting Fixture)
Weight per unit	N/A
Product Category	Electrical Fixture Conn (Nuts

Features

connection	2 Ports
Voltage Rating	600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures
Wire Size	#12 AWG - #20 AWG Solid, #12 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand) Stranded, #14 AWG - #18 AWG (19 Strand Or Less) Stranded (Tin Bonded)
Wire Type	Solid, Stranded, Stranded (Tin Bonded)

Material, Color, and Finish

Color	Red
-------	-----

Dimensions and Weight

Size	0.780 IN Length X 0.520 IN Width X 0.380 IN Height
------	--

Descriptions

Description	IN-SURE PUSH-IN CONN, 32 2-PORT RED, 300/JAR
extra long description	IDEAL 30-1032J PUSH-IN 12AWG 2-PORT
Features	Ergonomic design for easy grip and comfortable installationLow insertion force for fast and easy connectionsCompact size makes installation easyClear shell gives visual verification of connectionTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Approved for bonding and grounding applicationsStrip, push, connect – the fastest way to make a connection.The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch c

Manufacturer Information

Brand	Ideal
GTIN	00783250693528
UPC	783250693528



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....WIRE NUTS

Type.....Push-In

Availability

minimum qty.....300

Packaging

Carton.....1800

Weight Per each.....0

Uses, Certifications, and Standards

standard.....CSA C22.2 #188, 486C/467 UL Listed, RoHS

Temperature Rating.....105 DEG C Shell Rated