



30190S

F40T12 BL (PK X 15)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Diameter: 1.50 IN

Length: 48.00 IN

Package Weight: 13.40 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 40.0 W

Average Life Hours: 20000

Bulb: T12

Color: Black Light

Lamp Type: Fluorescent

Package (LxWxH): 49.25 IN x 5.50 IN x 8.75 IN

Pack By: 15

Special Features: Shatter-Resistant

UPC: 726585301904

ULEPH,ROHS,NSF Splash Zone



30190S

F40T12 BL (PK X 15)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Diameter: 1.50 IN

Length: 48.00 IN

Package Weight: 13.40 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 40.0 W

Average Life Hours: 20000

Bulb: T12

Color: Black Light

Lamp Type: Fluorescent

Package (LxWxH): 49.25 IN x 5.50 IN x 8.75 IN

Pack By: 15

Special Features: Shatter-Resistant

UPC: 726585301904

ULEPH,ROHS,NSF Splash Zone