


73 Fresnel Lens



73P White Trim with Fresnel Glass Lens
73PS White Trim with Fresnel Glass Lens, Wet Location




HOUSING / LAMP:
H7RT: 60W A19
H7T: 60W A19
H7TCP: 60W A19

DIMENSIONS: OD: 8" [203mm]

173 Fresnel Lens with Reflector



173P White Trim with Fresnel Glass Lens
173PS White Trim with Fresnel Glass Lens, Wet Location, AIR-TITE™




HOUSING / LAMP:
H7TNB: 60W A19

DIMENSIONS: Height: 4" [101mm]; OD: 8" [203mm]

75 Diffuser



75 All Glass Diffuser




HOUSING / LAMP:
H7RT: 60W A19
H7T: 60W A19
H7TCP: 60W A19

DIMENSIONS: OD: 7-3/4" [197mm]

172 Dome Lens with Reflector



172PS White Trim with Frosted Glass Dome, Wet Location, AIR-TITE™
172SNS Satin Nickel Trim with Frosted Glass Dome, Wet Location, AIR-TITE™
172TBZS Tuscan Bronze Trim with Frosted Glass Dome, Wet Location, AIR-TITE™




HOUSING / LAMP:
H7RT: 50W PAR30, 60W A19
H7T: 75W PAR30, 100W A19
H7TNB: 75W PAR30, 100W A19
H7TCP: 75W PAR30, 100W A19

DIMENSIONS: Height: 2-1/8" [54mm]; OD: 7-3/4" [197mm]

416 Regressed Diffuser



416P White Trim and Regressed Diffuser, Black Baffle
416W White Trim and Regressed Diffuser, White Baffle




HOUSING / LAMP:
H7RT: 60W A19
H7T: 60W A19
H7TCP: 60W A19

DIMENSIONS: Aperture: 5-3/4" [146mm]; OD: 7-1/4" [184mm]

300 Open Trim with Socket Support



300P White Trim
300SN Satin Nickel Trim
300TBZ Tuscan Bronze Trim




HOUSING / LAMP:
H7T: 65W BR30, 75W PAR30, 75W PAR30L, 75W R30
H7TNB: 65W BR30, 75W PAR30, 75W PAR30L, 75W R30
H7TCP: 65W BR30, 75W PAR30, 75W PAR30L, 75W R30

DIMENSIONS: Height: 4" [102mm]; OD: 7-1/4" [184mm]

301 Open Trim



301P White Trim
301SN Satin Nickel Trim
301TBZ Tuscan Bronze Trim
301PB Polished Brass Trim




HOUSING / LAMP:
H7RT: 65W BR30, 75W R30, 75W PAR30, 75W PAR30L
H7T: 65W BR30, 75W R30, 75W PAR30
H7TCP: 65W BR30, 75W R30, 75W PAR30

DIMENSIONS: OD: 7-1/4" [184mm]

401 Open Trim



401P White Trim
401AL Satin Aluminum Trim
401PB Polished Brass Trim




HOUSING / LAMP:
H7RT: 120W BR40, 150W R40
H7T: 120W BR40, 150W R40
H7TCP: 120W BR40, 150W R40

DIMENSIONS: OD: 8" [203mm]

328 White Splay Trim



328P White Splay Trim




HOUSING / LAMP:
H7RT: 65W BR30, 75W R30, 75W PAR30, 75W PAR30L
H7T: 65W BR30, 75W R30, 75W PAR30
H7TCP: 65W BR30, 75W R30, 75W PAR30

DIMENSIONS: Height: 3-7/8" [98mm]; OD: 7-3/4" [197mm]

428 White Splay Trim



428P White Splay Trim




HOUSING / LAMP:
H7RT: 120W BR40, 150W R40
H7T: 120W BR40, 150W R40
H7TCP: 120W BR40, 150W R40

DIMENSIONS: Aperture: 3-7/8" [98mm]; OD: 7-3/4" [197mm]

79 Pinhole Trim



79P White Trim




HOUSING / LAMP:
H7T: 50W R20
H7TCP: 50W R20

DIMENSIONS: OD: 8" [203mm]

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.

303 Wall Wash



303P White Trim and Scoop

HOUSING / LAMP:
 H7RT: 60W A19
 H7T: 60W A19
 H7TCP: 60W A19

DIMENSIONS: OD: 8" [203mm]

424 Wall Wash / Reflector Downlight




424P White Trim

HOUSING / LAMP:
 H7RT: 100W A19
 H7T: 100W A19
 H7TCP: 100W A19

DIMENSIONS: OD: 7-1/4" [184mm]

425 Wall Wash with Coilex® Baffle and Scoop




425W White Trim with White baffle
 425P White Trim with Black Baffle

HOUSING / LAMP:
 H7RT: 60W A19
 H7T: 60W A19
 H7TCP: 60W A19

DIMENSIONS: OD: 7-1/4" [184mm]

430 Wall Wash with Baffle and Full Reflector




430W White Trim with White Baffle, AIR-TITE™
 430P White Trim with Black Baffle, AIR-TITE™

HOUSING / LAMP:
 H7T: 90W TB19, 100W A19, 100W BT15, 100W MB19
 H7TNB: 90W TB19, 100W A19, 100W BT15, 100W MB19
 H7TCP: 90W TB19, 100W A19, 100W BT15, 100W MB19

DIMENSIONS: Height: 5" [127mm]; OD: 7-1/4" [184mm]

1412 Low Voltage Adj Spot 30° Tilt




1412W White Trim with White Baffle and Lampholder
 1412P White Trim with Black Baffle and Lampholder

HOUSING / LAMP:
 H7RT: 50W 12V MR16
 H7T: 50W 12V MR16
 H7TCP: 50W 12V MR16

DIMENSIONS: Aperture: 1-3/4" [44mm]; OD: 7-1/4" [184mm]

ACCESSORIES: Low Voltage Transformer Included

1416 Low Voltage Specular Reflector 30° Tilt




1416C White Trim with Clear Specular Reflector

HOUSING / LAMP:
 H7RT: 50W 12V MR16
 H7T: 50W 12V MR16
 H7TNB: 50W 12V MR16
 H7TCP: 50W 12V MR16

DIMENSIONS: OD: 7-1/4" [184mm]

ACCESSORIES: Low Voltage Transformer Included

1416 Low Voltage Baffle 30° Tilt




1416W White Trim with White Baffle
 1416BA White Trim with Black Baffle

HOUSING / LAMP:
 H7RT: 50W 12V MR16
 H7T: 50W 12V MR16
 H7TNB: 50W 12V MR16
 H7TCP: 50W 12V MR16

DIMENSIONS: OD: 7-1/4" [184mm]

ACCESSORIES: Low Voltage Transformer Included

1417 Low Voltage Eyeball with Baffle 30° Tilt




1417W White Trim with White Eyeball and White Baffle
 1417BA White Trim with White Eyeball and Black Baffle

HOUSING / LAMP:
 H7RT: 50W 12V MR16
 H7T: 50W 12V MR16
 H7TCP: 50W 12V MR16

DIMENSIONS: OD: 7-1/4" [184mm]

ACCESSORIES: Low Voltage Transformer Included

1450 Low Voltage Slot Aperture 30° Tilt




1450P White Slot Aperture Trim

HOUSING / LAMP:
 H7RT: 50W 12V MR16
 H7T: 50W 12V MR16
 H7TCP: 50W 12V MR16

DIMENSIONS: OD: 7-1/4" [184mm]

ACCESSORIES: Low Voltage Transformer Included

1475 Low Voltage Adjustable Accent 30° Tilt




1475W White Trim with White Baffle
 1475P White Trim with Black Baffle

HOUSING / LAMP:
 H7RT: 50W PAR36 low voltage
 H7T: 50W PAR36 low voltage
 H7TNB: 50W PAR36 low voltage
 H7TCP: 50W PAR36 low voltage

DIMENSIONS: OD: 7-1/4" [184mm]

ACCESSORIES: Low Voltage Transformer Included

1479 Low Voltage Pinhole Trim



2479W White Trim with White Baffle
 1479P White Trim with Black Baffle

HOUSING / LAMP:
 H7RT: 50W 12V MR16
 H7T: 50W 12V MR16
 H7TCP: 50W 12V MR16

DIMENSIONS: Aperture: 1-7/8" [48mm]; OD: 8" [203mm]

ACCESSORIES: Low Voltage Transformer Included

Specifications and dimensions subject to change without notice. Consult your Cooper Lighting Representative or visit www.cooperlighting.com for available options, accessories and ordering information.