



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 303628 Hi-Temp Wire-Nut Wire Conn, 72B Black, 100/Box

*Ideal*

|                  |  |
|------------------|--|
| Catalog Number   | 303628   |
| Manufacturer     | Ideal  |
| Description      | Ideal, Wire Connector, Wire-Nut, High Temperature Twist-On, Number Of Conductors: 1 to 5, Conductor Range: 22 - 14 Awg, Min 2 - 22, Max 3-16, Environmental Conditions: Tough, UI 94V-0 Flame-Retardant Shell Rated At 150 Deg C (302 F), Material: Thermoplastic Polyester, Color: Black, Voltage Rating: 300 V, Model Number: 72B, Width: 25/64 In, Height: 45/64 In |
| Weight per unit  | N/A  |
| Product Category | Patch Cords & Jumpers For VDV  |

### Features

|                |                         |
|----------------|-------------------------|
| Material       | THERMOPLASTIC POLYESTER |
| Voltage Rating | 300                     |

### Material, Color, and Finish

|       |       |
|-------|-------|
| Color | Black |
|-------|-------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | HI-TEMP WIRE-NUT WIRE CONN, 72B BLACK, 100/BOX   |
| extra long description | IDEAL 30-3628 100 PACK 72B BLACK   |
| Features               | The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame |
| Long Description       | IDEAL, Wire Connector, Wire-Nut, High Temperature Twist-On, Number Of Conductors: 1 to 5, Conductor Range: 22 - 14 AWG, Min 2 - 22, MAX 3-16, Environmental Conditions: Tough, UL 94V-0 Flame-Retardant Shell Rated At 150 DEG C (302 F), Material: THERMOPLASTIC POLYESTER, Color: Black, Voltage Rating: 300 V, Model Number: 72B, Width: 25/64 IN, Height: 45/64 IN   |
| Product Type           | 100 Pack 72B Black   |
| Special Features       | Deep Skirt Helps Protect Against Flash-Over;Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time;Height: 45/64 IN;Model Number: 72B;No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation;Reusable For Easy Circuit Changes And Additions;Tough, UL94V-0 Flame-Retardant Shell Rated At 150 Degree C (302 Degree F);UL Listed To 486C And CSA Certified To C22.2 #188;Width: 25/64 IN   |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Ideal          |
| GTIN                      | 00783250455409 |
| Manufacturers Part Number | 30-3628        |
| UPC                       | 783250455409   |

## Taxonomies, Classifications, and Categories

|                      |                           |
|----------------------|---------------------------|
| Category Description | WIRE NUTS                 |
| Type                 | High Temperature Twist-On |

## Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 100 |
| Weight Per each | 0   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Insulating or Joining 2 or more conductors in conditions where extreme heat buildup occurs such as high wattage fixtures and signs.

environmental conditions

Tough, UL 94V-0 Flame-Retardant Shell Rated At 150 DEG C (302 F)

standard

CSA Certified to C22.2 #188, UL Listed to 486C