



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30654 Wing-Nut Wire Conn, Model 454 Blue, 100/Bag

Ideal

Catalog Number	30654
Manufacturer	Ideal
Description	Ideal, Wire Connector, Wing-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Conductor Range: 14 - 6 Awg, Min 3 - 12, Max 1-6 W/2-8, Material: Flame-Retardant Polypropelene Shell, Color: Blue, Voltage Rating: 600 V, Model Number: 454, Flammability Rating: UL94V-2
Weight per unit	0.0190 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-retardant polypropelene shell
Voltage Rating	600

Material, Color, and Finish

Color	Blue
-------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WING-NUT WIRE CONN, MODEL 454 BLUE, 100/BAG
extra long description	IDEAL 30-654 WINGNUT 454 BLUE, 100
Features	Largest range in the Industry - from 2 #18 to up 4 #10High-leverage, contoured wing provides superior torque on every twistWide range, live-action spring handles small combinations and expands to accommodate large combinations as you need itCopolymer shell expands for smooth, progressive tightening providing dependable connectionsRemovable for repeat usage on same size or larger combinationsMore power with every twist.The Wing-Nut Wire Connector provides an easy, secure grip when connecting a wide range of
Long Description	IDEAL, Wire Connector, Wing-Nut, Twist-On, Number Of Conductors: 1 to 6, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Conductor Range: 14 - 6 AWG, Min 3 - 12, MAX 1-6 w/2-8, Material: Flame-retardant polypropelene shell, Color: Blue, Voltage Rating: 600 V, Model Number: 454, Flammability Rating: UL94V-2
Product Type	Wingnut 454 Blue, 100 Bag
Special Features	Comply With Federal Specification W-S-610E;Deep skirt helps protect against flash-over and turned-back strands for maximum dielectric protection;Features: Specially designed contour wings provide a secure grip for extra leverage;Flammability Rating: UL94V-2;Live action Spring expands to accept wire shape abd size with no pre-twisting required;Model Number: 454;Square wire spring threads directly onto conductors for fast, secure connections;Togh UL 94V-2 flame-retardent shell rated at 105 deg c(221 deg F);U

Manufacturer Information

Brand	Ideal
GTIN	00783250306541
Manufacturers Part Number	30-654
UPC	783250306541

Taxonomies, Classifications, and Categories

Category Description	WIRE NUTS
Type	Twist-On

Packaging

Carton	100
Package	1000
Weight Per each	0.019



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E, RoHS Compliant