


# CARBIDE HOLE CUTTER

Designed Specifically for Sheet Metal Hole Cutting



## Specifications (1 per box)

Product Number	Diameter (Inches)	Conduit Size (Inches)	Arbor
20091-11CHC	11/16		5L
20092-12CHC	3/4		5L
20093-14CHC	7/8	1/2	5L
20094-16CHC	1		5L
20095-17CHC	1-1/16		5L
20096-18CHC	1-1/8	3/4	5L
20097-19.5CHC	1-7/32		5L
20098-20CHC	1-1/4		3L
20099-21CHC	1-5/16		3L
20100-22CHC	1-3/8		3L
20101-23CHC	1-7/16		3L
20102-24CHC	1-1/2		3L
20103-28CHC	1-3/4	1-1/4	3L
20104-32CHC	2	1-1/2	3L
20105-34CHC	2-1/8		3L
20106-36CHC	2-1/4		3L
20107-38CHC	2-3/8		3L
20108-40CHC	2-1/2	2	3L
20109-42CHC	2-5/8		3L
20113-44CHC	2-3/4		3L
20114-48CHC	3		3L

Accessories	Description
30879-35PD	1/4" split point stubby pilot bit
30880-3CHC-AS	Plug ejection springs
30003-3L	1/2" arbor for 20CHC – 48CHC. Solid hex shank
30005-5L	3/8" arbor for 11CHC – 19.5CHC. Solid hex shank

## THE LENOX® ADVANTAGE™

- Accurate, burr-free holes**  
 Precision ground carbide teeth for fast cutting of clean, round holes.
- Long tool life**  
 Heat resistant carbide teeth for long life in sheet metal and stainless steel.
- Will not damage work**  
 Over-drill stopper prevents the tool from penetrating beyond the hole.
- Starts on contact**  
 Split point pilot bit for faster penetration and less walking.
- Use standard arbor**



### 12 Piece, Electrician Kit

Product No. 30877-300CHC  
 7/8", 1-1/8", 1-3/8". Arbors: 3L, 5L. 1/4" split point pilot bit. Plug ejection springs. 1/8" hex wrench. Plastic case.




### 14 Piece, Electrician Kit

Product No. 30878-500CHC  
 7/8", 1-1/8", 1-3/8", 1-3/4", 2". Arbors: 3L, 5L. 1/4" split point pilot bit. Plug ejection springs. 1/8" hex wrench. Plastic case.

# CARBIDE HOLE CUTTER

Designed Specifically for Sheet Metal Hole Cutting



## Specifications (1 per box)

Product Number	Diameter (Inches)	Conduit Size (Inches)	Arbor
20091-11CHC	11/16		5L
20092-12CHC	3/4		5L
20093-14CHC	7/8	1/2	5L
20094-16CHC	1		5L
20095-17CHC	1-1/16		5L
20096-18CHC	1-1/8	3/4	5L
20097-19.5CHC	1-7/32		5L
20098-20CHC	1-1/4		3L
20099-21CHC	1-5/16		3L
20100-22CHC	1-3/8		3L
20101-23CHC	1-7/16		3L
20102-24CHC	1-1/2		3L
20103-28CHC	1-3/4	1-1/4	3L
20104-32CHC	2	1-1/2	3L
20105-34CHC	2-1/8		3L
20106-36CHC	2-1/4		3L
20107-38CHC	2-3/8		3L
20108-40CHC	2-1/2	2	3L
20109-42CHC	2-5/8		3L
20113-44CHC	2-3/4		3L
20114-48CHC	3		3L

Accessories	Description
30879-35PD	1/4" split point stubby pilot bit
30880-3CHC-AS	Plug ejection springs
30003-3L	1/2" arbor for 20CHC – 48CHC. Solid hex shank
30005-5L	3/8" arbor for 11CHC – 19.5CHC. Solid hex shank

## THE LENOX® ADVANTAGE™

- **Accurate, burr-free holes**  
Precision ground carbide teeth for fast cutting of clean, round holes.
- **Long tool life**  
Heat resistant carbide teeth for long life in sheet metal and stainless steel.
- **Will not damage work**  
Over-drill stopper prevents the tool from penetrating beyond the hole.
- **Starts on contact**  
Split point pilot bit for faster penetration and less walking.
- **Use standard arbor**



### 12 Piece, Electrician Kit

Product No. 30877-300CHC  
7/8", 1-1/8", 1-3/8". Arbors: 3L, 5L. 1/4" split point pilot bit. Plug ejection springs. 1/8" hex wrench. Plastic case.



### 14 Piece, Electrician Kit

Product No. 30878-500CHC  
7/8", 1-1/8", 1-3/8", 1-3/4", 2". Arbors: 3L, 5L. 1/4" split point pilot bit. Plug ejection springs. 1/8" hex wrench. Plastic case.