

VARI-BIT® STEP DRILL BITS

Drills Fast, Clean, Round Holes



LENOX® VARI-BIT® Kits



4 Piece (1/8"–1")
Product No.
30926-VBK-4
 4 sizes: VB1, VB2, VB7,
 VB8. Instruction sheet.
 Plastic case.



4 Piece (1/8"–1-3/8")
Product No.
30929-30/929
 4 sizes: VB1, VB3, VB8,
 VB12. Instruction sheet.
 Plastic case.



4 Piece (3/16"–1-1/8")
Product No.
30928-VBKE
 4 sizes: VB3, VB6, VB8,
 VB11. Instruction sheet.
 Plastic case.



6 Piece (1/8"–1-1/8")
Product No.
30927-VBKA-6
 6 sizes: VB1, VB2, VB6,
 VB7, VB8, VB11.
 Instruction sheet.
 Plastic case.



3 Piece (1/8"–1")
Product No.
30889-889
 3 sizes: VB1, VB2, VB3.
 Instruction sheet.
 Plastic case.

THE LENOX® ADVANTAGE™

- **Accurate, burr-free holes**
Patented two flute design cuts fast, clean, round holes.
- **Starts on contact**
Split point design for faster penetration and less walking.
- **Long tool life**
Steam oxide coating adds durability. Enhanced flute design removes chips rapidly, ensuring longer tool life.

Specifications (1 per pack)

U.S. PATENT NO. 4582458

Product Number	Photo	Hole Sizes (Inches)	Chuck Size (Inches)	Unibit®	Klein Unibit®
30881-VB1		1/8, 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 13/32, 7/16, 15/32, 1/2	1/4	1	1-59001
30882-VB2		1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1	3/8	20	2-59002
30883-VB3		1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4	3/8	3	3-59003
30884-VB4		3/16, 1/4, 5/16, 3/8, 7/16, 1/2	1/4	2	5-59005
30886-VB6		3/8, 1/2	1/4	10, 12*	7-59007
30887-VB7		7/8 (for 1/2" conduit)	3/8	11	8-59008
30908-VB8		3/16, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8	3/8	4	14-590014
30909-VB9		7/8, 1-1/8, 1-7/32	3/8	11, 13, 14	59011
30888-VB11		7/8, 1-1/8 (for 1/2" and 3/4" conduit)	3/8	13**	11-590011
30912-VB12		7/8, 1-1/8, 1-7/32, 1-1/4, 1-3/8	3/8	none	none
30925-VBX8		Extension 8" Fits 3/8" drill chuck & larger. 1 per clam			

* LENOX® VARI-BIT® #6 combines Unibit® #10 & #12.

** Unibit® #13 has 1-1/8" step only. VARI-BIT® has both 7/8" & 1-1/8".

VARI-BIT® STEP DRILL BITS

Drills Fast, Clean, Round Holes



LENOX® VARI-BIT® Kits



4 Piece (1/8"–1")
Product No.
30926-VBK-4
 4 sizes: VB1, VB2, VB7, VB8. Instruction sheet. Plastic case.



4 Piece (1/8"–1-3/8")
Product No.
30929-30/929
 4 sizes: VB1, VB3, VB8, VB12. Instruction sheet. Plastic case.



4 Piece (3/16"–1-1/8")
Product No.
30928-VBKE
 4 sizes: VB3, VB6, VB8, VB11. Instruction sheet. Plastic case.



6 Piece (1/8"–1-1/8")
Product No.
30927-VBKA-6
 6 sizes: VB1, VB2, VB6, VB7, VB8, VB11. Instruction sheet. Plastic case.



3 Piece (1/8"–1")
Product No.
30889-889
 3 sizes: VB1, VB2, VB3. Instruction sheet. Plastic case.

THE LENOX® ADVANTAGE™

- **Accurate, burr-free holes**
Patented two flute design cuts fast, clean, round holes.
- **Starts on contact**
Split point design for faster penetration and less walking.
- **Long tool life**
Steam oxide coating adds durability. Enhanced flute design removes chips rapidly, ensuring longer tool life.

Specifications (1 per pack)

U.S. PATENT NO. 4582458

Product Number	Photo	Hole Sizes (Inches)	Chuck Size (Inches)	Unibit®	Klein Unibit®
30881-VB1		1/8, 5/32, 3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 13/32, 7/16, 15/32, 1/2	1/4	1	1-59001
30882-VB2		1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8, 15/16, 1	3/8	20	2-59002
30883-VB3		1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4	3/8	3	3-59003
30884-VB4		3/16, 1/4, 5/16, 3/8, 7/16, 1/2	1/4	2	5-59005
30886-VB6		3/8, 1/2	1/4	10, 12*	7-59007
30887-VB7		7/8 (for 1/2" conduit)	3/8	11	8-59008
30908-VB8		3/16, 1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4, 13/16, 7/8	3/8	4	14-590014
30909-VB9		7/8, 1-1/8, 1-7/32	3/8	11, 13, 14	59011
30888-VB11		7/8, 1-1/8 (for 1/2" and 3/4" conduit)	3/8	13**	11-590011
30912-VB12		7/8, 1-1/8, 1-7/32, 1-1/4, 1-3/8	3/8	none	none
30925-VBX8		Extension 8" Fits 3/8" drill chuck & larger. 1 per clam			

* LENOX® VARI-BIT® #6 combines Unibit® #10 & #12.

** Unibit® #13 has 1-1/8" step only. VARI-BIT® has both 7/8" & 1-1/8".