



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



31355 Yellow 77, 5-Gallon Bucket

Ideal

Catalog Number	31355
Manufacturer	Ideal
Description	Yellow 77 Lubricant, Size: 5 Gal, Container: Bucket, Specific Gravity: 0.98, Plastic Safe: Yes, Slight Perfume Odor, Voc: 2.7 GPL (As Packaged, Minus Water), Working Temperature: 40 - 100 Deg F, Boiling Point: 212 Deg F (100 Deg C), Percent Volatile By Volume: Less Than 90 PCT, Percent Solid By Weight: Approximately 20 PCT, Yellow Paste, 7 - 8.5 PH, Solubility In Water: Moderate, Storage Temperature: 32 - 130 Deg F, UI Listed, For Wire Pulling
Weight per unit	43.0 (lbs/each)
Product Category	Paint, Chemicals, Etc.

Features

odor	Slight Perfume
specific gravity	0.98

Dimensions and Weight

Size	5
------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	YELLOW 77, 5-GALLON BUCKET
extra long description	IDEAL 31-355 Yellow Lubricant,Ideal
Features	IDEAL Yellow 77 Wire pulling lubricant is a wax-based formula, and is the perfect general purpose lube. It is safe to use with most cable types except low-density polyethylene and semi-conducting jackets. It won't break down/separate after repeated exposure to freezing temperatures and dries to a thin, non-conductive film that won't clog conduit. Yellow 77 has a creamy texture and clings to cable throughout long pulls. Apply conveniently and uniformly by hand or brush. It is a homogeneous blend that requir
Long Description	Yellow 77 Lubricant, Size: 5 GAL, Container: Bucket, Specific Gravity: 0.98, Plastic Safe: Yes, Slight Perfume Odor, Voc: 2.7 GPL (As Packaged, Minus Water), Working Temperature: 40 - 100 DEG F, Boiling Point: 212 DEG F (100 DEG C), Percent Volatile By Volume: Less Than 90 PCT, Percent Solid By Weight: Approximately 20 PCT, Yellow Paste, 7 - 8.5 pH, Solubility In Water: Moderate, Storage Temperature: 32 - 130 DEG F, UI Listed, For Wire Pulling
Product Type	Yellow Lubricant, Ideal, 5 Gal Bucket Capacity, For 77 Wire Pul
Special Features	The #1 brand of wire pulling lubricant since 1959 - the perfect general purpose lube; Wax-based formula provides superior lubricity; Safe to use with most cable types except low-density polyethylene and semi-conducting jackets; Won't break down or separate after repeated exposure to freezing temperatures; Dries to a thin, non-conductive film that won't clog conduit; Clings to cable throughout long pulls; Easy to apply by hand or with pump; Creamy texture applies easily and uniformly; Homogeneous blend requ

Manufacturer Information

Brand	Ideal
GTIN	00783250313556
Manufacturers Part Number	31-355
UPC	783250313556

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Lubricant

Packaging

Carton	1
Weight Per each	43



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For Wire Pulling
standard	UL Listed