



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 3201TB 1/2 NM Cable Connector

*Abb Installation Products, Inc*

Catalog Number	3201TB
Manufacturer	Abb Installation Products, Inc
Description	Fitting, Non-Metallic Sheathed Cable, Knockout Size 1/2 Inch, Length 1-11/32 Inch, Height 1 Inch, Hole Size 2-1/32 Inch Diameter, Thermoplastic, For Use With 10-3, 12-3, 14-3, 10-2, 12-2, 4-2 Non-Metallic Cables, Multiple (2) 12-2 and 14-2 Non-Metallic Cables, Single and Multiple Flexible Cords In Wire Range .300-.600 Inch
Weight per unit	0.0200 (lbs/each)
Product Category	Non-Metallic CBL CBL Fittings

### Features

Material	Non-Metallic
----------	--------------

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	1/2 INCH
------	----------

### Descriptions

Description	1/2 NM CABLE CONNECTOR
extra long description	ABB 3201-TB 1/2 CONN,NM CABLE/FLEX
Long Description	Fitting, Non-Metallic Sheathed Cable, Knockout Size 1/2 Inch, Length 1-11/32 Inch, Height 1 Inch, Hole Size 2-1/32 Inch Diameter, Thermoplastic, For use with 10-3, 12-3, 14-3, 10-2, 12-2, 4-2 Non-Metallic Cables, Multiple (2) 12-2 and 14-2 Non-Metallic Cables, Single and Multiple Flexible Cords in Wire Range .300-.600 Inch
Product Type	1/2 Conn, NM Cable/Flex Cord, NM

### Manufacturer Information

Brand	Steel City
GTIN	00786210032016
Manufacturers Part Number	3201-TB
UPC	786210032016

### Taxonomies, Classifications, and Categories

Category Description	PVC CONDULETS
Type	Connectors-Straight



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	50
Package	500
Weight Per each	0.02

## Uses, Certifications, and Standards

Application	For use with non-metallic sheathed cable and flexible cord
standard	UL e17583 / UL e17583