



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



323022BU Bulk 4-Way Splitter

Waldom Electronics CO.

Catalog Number	323022BU
Manufacturer	Waldom Electronics CO.
Description	GC Waldom Electronics; Splitter; High Quality Broadcast, Hybrid; Frequency Range: 5 - 900 MHZ; Insertion Loss: 6.8 DB (VHF)/7.2 DB (Uhf); Input: 75 Ohm Video Signal; Output: 75 Ohm Multiple Video Outlets; Isolation: 25 DB (VHF)/20 DB(Uhf) (Out-Out); Retur
Weight per unit	N/A
Product Category	Couplrs, SPLTTRS, Switches, At

Features

connector	F-Type
Frequency Range	5 - 900
Impedance	51898
input	75 OHM Video Signal
Number of Ways	798
output	75 OHM Multiple Video Outlets

Descriptions

Description	BULK 4-WAY SPLITTER
extra long description	5 TO 900 MHZ FREQUENCY RATING; 4 WAY(S); GC[T] BRAND
Long Description	GC Waldom Electronics; Splitter; High Quality Broadcast, Hybrid; Frequency Range: 5 - 900 MHZ; Insertion Loss: 6.8 DB (VHF)/7.2 DB (UHF); Input: 75 OHM Video Signal; Output: 75 OHM Multiple Video Outlets; Isolation: 25 DB (VHF)/20 DB(UHF) (Out-Out); Retur
Product Type	Splitter, GC Waldom Electronics, High Quality Broadcast, Hybrid
Special Features	All terminals use standard threaded "F" video connectors; Anti-corrosion plating and sealed case resist the elements; These splitters feature a built in ground block; Nickel plating; Package: Bulk Pack

Manufacturer Information

Brand	GC/Waldom Electronics
GTIN	00010151326270
Manufacturers Part Number	32-3022-00BU
UPC	010151326270

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	High Quality Broadcast Hybrid Splitter



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Inactive

Packaging

Carton 10

Weight Per each 0

Uses, Certifications, and Standards

standard RoHS Compliant