



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

3232TRWR TR WR Duplex Recp 15A/125V BN

Pass & Seymour/Legrand

Catalog Number	3232TRWR
Manufacturer	Pass & Seymour/Legrand
Description	Duplex Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #12 Awg Compatible Wire Size, Side Wire;Push Wire Connection, Wall Mount, 1.320 In Length, 1.0 In Width, 4.20 In Height, Thermoplastic, Brown, Weather Resistant;Tamper Resistant, Impact Resistant, 0.1400 LB
Weight per unit	0.1352 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Side wire, push wire
indoor/outdoor	Outdoor
Outlet Type	Residential, Outdoor, Commercial, Tamper-Resistant, Weather-Resistant
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wattage	Electrical power is expressed in Amps and Volts.
Wire Size	14 - 12

Material, Color, and Finish

Finish	Matte
--------	-------

Descriptions

Description	TR WR DUPLEX RECP 15A/125V BN
extra long description	P&S 3232TRWR TR WR DUP REC 15A/125V

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007241747
Manufacturers Part Number	3232TRWR
UPC	785007241747

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Outlet

Trade Size

Amperage	15.0
----------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	200
Weight Per each	0.1352

Uses, Certifications, and Standards

environmental conditions	Flammability: UL94 V2
Mounting	WALL
standard	CULUS, cULus UL498, CSA C22.2 No. 42