



15A/125V WEATHER-RESISTANT DUPLEX RECEPTACLE, LIGHT ALMOND

3232TRWRLA | [Pass & Seymour](#)

FEATURES & BENEFITS

Whether you need to plug in a hedge trimmer, light a driveway, pathway or deck, or enjoy your favorite music by the pool, our Pass & Seymour weather-resistant receptacles are the better solution. And since this receptacle is tamper resistant as required by the National Electrical Code® (NEC®), you can feel confident that your children will be protected.



PRODUCT ENVIRONMENTAL PROFILE

- Residential Weather-Resistant Receptacles are Tamper-Resistant as required by 2008 National Electrical Code.
- Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including: Ultraviolet light exposure test; Cold impact test; Accelerated aging test; Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- WR markings on face per UL Weather-Resistant requirements.
- Patented internal shutter system lets plugs in, but keeps keys and other objects out with automatic shutters that block access.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Low profile face.
- Traditional contoured face.
- High-impact resistant thermoplastic construction.
- Safer and more effective than plastic outlet caps.
- TR markings identify devices as Tamper-Resistant.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Type: Duplex
Number Of Poles: 2

Number Of Wires: 3
Special Features: Weather-Resistant

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.0"
Height (US): 3.31"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 125
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





15A/125V WEATHER-RESISTANT DUPLEX RECEPTACLE, LIGHT ALMOND

3232TRWRLA | [Pass & Seymour](#)

FEATURES & BENEFITS

Whether you need to plug in a hedge trimmer, light a driveway, pathway or deck, or enjoy your favorite music by the pool, our Pass & Seymour weather-resistant receptacles are the better solution. And since this receptacle is tamper resistant as required by the National Electrical Code® (NEC®), you can feel confident that your children will be protected.



PRODUCT ENVIRONMENTAL PROFILE

- Residential Weather-Resistant Receptacles are Tamper-Resistant as required by 2008 National Electrical Code.
- Listed to the Weather-Resistant supplement of UL498, meeting demanding UL requirements including: Ultraviolet light exposure test; Cold impact test; Accelerated aging test; Stringent material requirements for current-carrying parts, wire binding screws and mounting straps to ensure superior corrosion resistance.
- WR markings on face per UL Weather-Resistant requirements.
- Patented internal shutter system lets plugs in, but keeps keys and other objects out with automatic shutters that block access.
- Side wire accepts #12 – #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Low profile face.
- Traditional contoured face.
- High-impact resistant thermoplastic construction.
- Safer and more effective than plastic outlet caps.
- TR markings identify devices as Tamper-Resistant.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Type: Duplex
Number Of Poles: 2

Number Of Wires: 3
Special Features: Weather-Resistant

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.0"
Height (US): 3.31"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 125
Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

