



15A/125V TRADEMASTER® DUPLEX RECEPTACLE, WHITE

3232W | [Pass & Seymour](#)

FEATURES & BENEFITS

Our Pass & Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.



- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs. Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only. Low profile face. Traditional contoured face.
- (3232 models) Self-grounding models provide automatic ground clip.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Duplex
Number Of Poles: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): .960"
Height (US): 3.31"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 125

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No



15A/125V TRADEMASTER® DUPLEX RECEPTACLE, WHITE

3232W | [Pass & Seymour](#)

FEATURES & BENEFITS

Our Pass & Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.



- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs. Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only. Low profile face. Traditional contoured face.
- (3232 models) Self-grounding models provide automatic ground clip.

SPECIFICATIONS

GENERAL INFO

Color: White
Type: Duplex
Number Of Poles: 2

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): .960"
Height (US): 3.31"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 125

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

Buy American Act Status: No