

# Eaton 32B-BOX

Catalog Number: 32B-BOX

Eaton power device receptacle, Range, #12 - 4 AWG, 50A, Flush, 125/250V, Back, Brown, NEMA 10-50R, Three-pole, Three-wire, Three-pole, three-wire, non grounding, Plug, Glass-filled nylon, Power, Used with S80

## General specifications



Photo is representative

### Product Name

Eaton power device receptacle

### Catalog Number

32B-BOX

### UPC

032664198403

### Product Length/Depth

8.5 in

### Product Height

2.25 in

### Product Width

6 in

### Product Weight

0.25 lb

### Compliances

NAFTA

RoHS Compliant

### Certifications

UL Listed

NOM



Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Used with

S80

### Special features

Range

### Amperage Rating

50 A

### Voltage rating

125/250 V

### Wiring method

Back

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Three-pole

### Color

Brown

### Connection type

Plug

### Style

Power

### Allowable wire size

#12-4 AWG

### NEMA configuration

10-50R

### Torque rating

25 lbf-inch

### Design type

Receptacle

### Material

Glass filled nylon

### Receptacle type

Three-pole, three-wire, non grounding

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 32B-BOX](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)

# Eaton 32B-BOX

Catalog Number: 32B-BOX

Eaton power device receptacle, Range, #12 - 4 AWG, 50A, Flush, 125/250V, Back, Brown, NEMA 10-50R, Three-pole, Three-wire, Three-pole, three-wire, non grounding, Plug, Glass-filled nylon, Power, Used with S80

## General specifications



Photo is representative

### Product Name

Eaton power device receptacle

### Catalog Number

32B-BOX

### UPC

032664198403

### Product Length/Depth

8.5 in

### Product Height

2.25 in

### Product Width

6 in

### Product Weight

0.25 lb

### Compliances

NAFTA

RoHS Compliant

### Certifications

UL Listed

NOM

## defaultTaxonomyAttributeLabel

### Used with

S80

### Special features

Range

### Amperage Rating

50 A

### Voltage rating

125/250 V

### Wiring method

Back

### Number of wires

3

### Mounting method

Flush

### Number Of Poles

Three-pole

### Color

Brown

### Connection type

Plug

### Style

Power

### Allowable wire size

#12-4 AWG

### NEMA configuration

10-50R

### Torque rating

25 lbf-inch

### Design type

Receptacle

### Material

Glass filled nylon

### Receptacle type

Three-pole, three-wire, non grounding

## Resources

### Brochures

[Flush mount receptacles sell sheet](#)

### Catalogs

[Arrow Hart Buyers Guide Section B](#)

### Specifications and datasheets

[Eaton Specification Sheet - 32B-BOX](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)