



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35083 Twist-A-Nut Conduit Deburring Tool, Slotted Tip

Ideal

Catalog Number	35083
Manufacturer	Ideal
Description	Ideal, Conduit Deburring Tool, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Weight per unit	0.3333 (lbs/each)
Product Category	Tool Kits

Descriptions

Description	TWIST-A-NUT CONDUIT DEBURRING TOOL, SLOTTED TIP
extra long description	IDEAL 35-083 TWIST-A-NUT CONDUIT DE
Features	Deburs inside and outside edges of 1/2 in., 3/4 in. and 1 in. thin wall conduit Hooded tip tightens EMT fitting set screws without slipping Square tip "seats" much more quickly on fitting screws than slotted version Head removes and is interchangeable with IDEAL 7-in-1 Twist-a-Nut Screwdriver shaft (#35-908) Head can be used at low speed setting in drill or cordless screwdriver
Long Description	IDEAL, Conduit Deburring Tool, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Product Type	Twist-A-Nut Conduit Deburrer
Special Features	Features: Deburs Inside And Outside Edges Of 1/2, 3/4, And 1 IN Thin Wall Conduit; Hooded Tip Tightens Emt Fitting Set Screws Without Slipping; Removable Head Interchangeable With Ideal 7-In-1 Twist -A-Nut Screwdriver Shaft (35-908); Head Can Be Used In Drill Or Cordless Screwdriver; Universal Wire-Nut Wrench In Handle End Eases Installation Of Twist-On Connectors; Lifetime Guarantee (Excludes Blades); Warranty: Lifetime Guarantee

Manufacturer Information

Brand	Ideal
GTIN	00783250350834
Manufacturers Part Number	35083
UPC	783250350834

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	SLOTTED TIP

Packaging

Carton	1
Weight Per each	0.3333