



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 35096 Twist-A-Nut Conduit Deburring Head Only, Slot Tip

*Ideal*

Catalog Number	35096
Manufacturer	Ideal
Description	Ideal, Conduit Deburring Tool Head, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Weight per unit	0.3500 (lbs/each)
Product Category	Hand Tool Bits, Parts, Acessor

### Descriptions

Description	TWIST-A-NUT CONDUIT DEBURRING HEAD ONLY, SLOT TIP
extra long description	IDEAL 35-096 CONDUIT DEBURR HEAD W
Features	Deburs inside and outside edges of 1/2 in., 3/4 in. and 1 in. thin wall conduitHooded tip tightens EMT fitting set screws without slippingSquare tip "seats" much more quickly on fitting screws than slotted versionHead removes and is interchangeable with IDEAL 7-in-1 Twist-a-Nut Screwdriver shaft (#35-908)Head can be used at low speed setting in drill or cordless screwdriverThe Twist-a-Nut Conduit deburring tool head is used with IDEAL 7-in-1 Twist -a-Nut screwdriver shaft to smooth inside/outside edges of
Long Description	IDEAL, Conduit Deburring Tool Head, Twist-A-Nut, Slotted Tip, Warranty: Lifetime Guarantee
Product Type	Conduit Deburr Head W Slot Tip
Special Features	Features: Deburrs Inside And Outside Edges Of 1/2, 3/4, And 1 IN Thin Wall Conduit; Hooded Tip Tightens Emt Fitting Set Screws Without Slipping; Removable Head Interchangeable With Ideal 7-In-1 Twist -A-Nut Screwdriver Shaft (35-908); Head Can Be Used In Drill Or Cordless Screwdriver; Universal Wire-Nut Wrench In Handle End Eases Installation Of Twist-On Connectors; Lifetime Guarantee (Excludes Blades); Warranty: Lifetime Guarantee

### Manufacturer Information

Brand	Ideal
GTIN	00783250583225
Manufacturers Part Number	35-096
UPC	783250583225

### Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	SLOTTED TIP

### Packaging

Carton	1
Weight Per each	0.35