



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35184 Cab Tip Screwdriver, 3/16 X 4"

Ideal

| | |
|------------------|--|
| Catalog Number | 35184 |
| Manufacturer | Ideal |
| Description | Ideal, Screwdriver, Electrician'S, Tip Size: 3/16 In, Overall Length: 7-3/4 In, Shank Length: 4 In, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Cabinet, Shank Size: 3/16 In |
| Weight per unit | 0.1833 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|--------------|-----------------------|
| Handle Type | Cushioned Rubber Grip |
| Shank Length | 4 |
| Tip Size | 3/16 |
| tip type | Cabinet |

Material, Color, and Finish

| | |
|----------------|-----------------------|
| Blade Material | Chrome Vanadium Steel |
|----------------|-----------------------|

Dimensions and Weight

| | |
|----------------|-------|
| Overall Length | 7-3/4 |
|----------------|-------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | CAB TIP SCREWDRIVER, 3/16 X 4" |
| extra long description | IDEAL 35-184 CAB TIP SCREWDRIVER, 3 |
| Features | These screwdrivers are made with nickel-chrome plating that is ideal for corrosion resistance. Plate chipping is prevented by a vapor-blasted tip. The screwdriver is 6-3/4-Inch long and features a tough, chrome vanadium steel round shank. The blade tip matches shank diameter for tough applications. Its cushion-grip handle is resistant to oil, gas and water and helps to prevent slippage for greater torque and superior comfort. It features a cross-ground tip to provide precise and secure fit in the screw slot. |
| Long Description | IDEAL, Screwdriver, Electrician's, Tip Size: 3/16 IN, Overall Length: 7-3/4 IN, Shank Length: 4 IN, Handle Type: Cushioned Rubber Grip, Blade Material: Chrome Vanadium Steel, Blade Finish: Nickel-Chrome Plating, Tip Type: Cabinet, Shank Size: 3/16 IN |
| Product Type | Cab Tip Screwdriver, 3 16X4" |
| Special Features | Features: Blade Tip Matches Shank Diameter; Vapor-Blasted Tip Prevents Plate Chipping; Cross-Ground Tip Provides Precise And Secure Fit In Screw Slot; Nickel-Chrome Plating For Corrosion Resistance; Tough, Chrome Vanadium Steel Shank; Cushioned Rubber Grip; Lifetime Guarantee; Identification Mark On Ends; Shank Size: 3/16 IN |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250351848 |
| Manufacturers Part Number | 35-184 |
| UPC | 783250351848 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------|
| Category Description | HAND TOOLS |
| Type | Electrician's |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Weight Per each | 0.1833 |