



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35598 Adjustable Can Light Hole Saw, 10 Sizes

Ideal

Catalog Number	35598
Manufacturer	Ideal
Description	Ideal, Hole Saw, Adjustable Can Light, Hole Diameter: 10 Sizes From 2-1/2 In to 7 In, Material: Stainless Steel Blade, Includes: 2 Dust Shields For Minimizing Mess, Finish: Carbide Coated Blade
Weight per unit	0.8400 (lbs/each)
Product Category	Power Tools - Corded

Features

Hole Diameter	10 Sizes From 2-1/2 IN To 7 IN
---------------	--------------------------------

Descriptions

Description	ADJUSTABLE CAN LIGHT HOLE SAW, 10 SIZES
extra long description	IDEAL 35-598 Hole Saw,Ideal,ADJ Can
Features	Cuts drywall and ceiling tileSelf-sharpening carbide-coated cutting bladesIncludes two dust shields to minimize clean up
Long Description	IDEAL, Hole Saw, Adjustable Can Light, Hole Diameter: 10 Sizes From 2-1/2 IN To 7 IN, Material: Stainless Steel Blade, Includes: 2 Dust Shields For Minimizing Mess, Finish: Carbide Coated Blade
Product Type	Hole Saw, Ideal, Adj Can LT, 10 Sizes From 2-1/2 In to 7.000 In
Special Features	Features: Infinitely Adjustable From 2-1/2 IN To 7 IN; Cuts Drywall And Ceiling Tile Only; Self-Sharpener Carbide Coated Stainless Steel Blades; Includes 2 Dust Shields For Minimizing Mess; Competitively Priced; Drill Not Included; Includes: 2 Dust Shields For Minimizing Mess; Finish: Carbide Coated Blade; Material: Tungsten Carbide Grit, High Speed Steel

Manufacturer Information

Brand	Ideal
GTIN	00783250550661
Manufacturers Part Number	35-598
UPC	783250550661

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Adjustable Can Light

Packaging

Carton	1
Weight Per each	0.84

Uses, Certifications, and Standards

Application	For Cutting Drywall And Ceiling Tile Only
standard	RoHS