



SNGL HELX SHORT SHIP AUGR 3/4



Features

- 62° reinforced cutting edge for added durability
- Precision ground, self-feeding lead screw
- Secondary relief angle for efficient chip removal
- Hardened lead screw and cutting edge powers through nails and staples and extends tool life
- Hardened & tempered shaft minimizes warping
- Quick-change shank design for fast bit changes and use with pneumatic drills
- 3/4" hole diameter
- Overall Length of 7 1/2"
- Twist Length of 5"

Models

Description	Catalog #
SNGL HELX SHORT SHIP AUGR 3/4	35-893



SNGL HELX SHORT SHIP AUGR 3/4



Features

- 62° reinforced cutting edge for added durability
- Precision ground, self-feeding lead screw
- Secondary relief angle for efficient chip removal
- Hardened lead screw and cutting edge powers through nails and staples and extends tool life
- Hardened & tempered shaft minimizes warping
- Quick-change shank design for fast bit changes and use with pneumatic drills
- 3/4" hole diameter
- Overall Length of 7 1/2"
- Twist Length of 5"

Models

Description	Catalog #
SNGL HELX SHORT SHIP AUGR 3/4	35-893