



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



3820 Straight Blade Recp 3P 4W 20A 125V

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 3820 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Straight Blade Receptacle 3-Pole 4-Wire 20A 125/250V |
| Weight per unit | 0.2170 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|------------|
| amperage rating | 20 |
| connection | Non Ground |
| Number of Wires | 4 |
| Poles | 3-way |
| Voltage | 125.0 V |
| Voltage Rating | 125/250 |
| Wire Size | 4 |

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | STRAIGHT BLADE RECP 3P 4W 20A 125V |
| extra long description | P&S 3820 STR BLD REC 3P 4W 20A 125V |
| Long Description | Straight Blade Receptacle 3-Pole 4-Wire 20A 125/250V |
| Product Type | STR BLD Rec 3P 4W 20A 125V |
| Special Features | Arc-resistant plastic, dead front design & double wire contact |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007790108 |
| Manufacturers Part Number | 3820 |
| UPC | 785007790108 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | Industrial receptacles |
| Type | Straight Blade Receptacle |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 20 |
| Weight Per each | 0.217 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Industrial Spec Grade |
| Mounting | WALL |
| nema rating | 14-20 |
| standard | UL, UL 498 |