

# Specifications



## Eaton 3MCB1000R

Eaton main circuit breaker, 1000A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, NGS, Four-wire, Three-phase, 120/208V, (4) #4/0 AWG-500 kcmil

### General specifications

<b>PRODUCT NAME</b>	Eaton main circuit breaker
<b>CATALOG NUMBER</b>	3MCB1000R
<b>UPC</b>	782116008278
<b>PRODUCT LENGTH/DEPTH</b>	13.8 in
<b>PRODUCT HEIGHT</b>	39.4 in
<b>PRODUCT WIDTH</b>	27 in
<b>PRODUCT WEIGHT</b>	160 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Neutral lugs order 1MCB1200NLK. Main devices with a rating greater than 800A can be used with 800A residential modular stacks, but only as a center fed main.

## Product specifications

<b>AMPERAGE RATING</b>	1000 A
<b>BUS MATERIAL</b>	Aluminum
<b>FEED TYPE</b>	Top/bottom
<b>PHASE</b>	Three-phase
<b>VOLTAGE RATING</b>	120/208 V
<b>UTILITY APPROVALS</b>	MI : DTE Energy (Detroit Edison) MD : Baltimore Gas and Electric DC : PEPCO MD : PEPCO NC : Dominion VA : Dominion
<b>ENCLOSURE</b>	NEMA 3R
<b>INTERRUPT RATING</b>	65 kAIC
<b>MAIN CIRCUIT BREAKER</b>	NGS
<b>NUMBER OF WIRES</b>	4
<b>WIRE SIZE</b>	(4) #4/0 AWG-500 kcmil

## Resources

<b>CATALOGS</b>	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - 3MCB1000R</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton 3MCB1000R

Eaton main circuit breaker, 1000A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, NGS, Four-wire, Three-phase, 120/208V, (4) #4/0 AWG-500 kcmil

### General specifications

<b>PRODUCT NAME</b>	Eaton main circuit breaker
<b>CATALOG NUMBER</b>	3MCB1000R
<b>UPC</b>	782116008278
<b>PRODUCT LENGTH/DEPTH</b>	13.8 in
<b>PRODUCT HEIGHT</b>	39.4 in
<b>PRODUCT WIDTH</b>	27 in
<b>PRODUCT WEIGHT</b>	160 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	Neutral lugs order 1MCB1200NLK. Main devices with a rating greater than 800A can be used with 800A residential modular stacks, but only as a center fed main.

## Product specifications

AMPERAGE RATING	1000 A
BUS MATERIAL	Aluminum
FEED TYPE	Top/bottom
PHASE	Three-phase
VOLTAGE RATING	120/208 V
UTILITY APPROVALS	MI : DTE Energy (Detroit Edison) MD : Baltimore Gas and Electric DC : PEPCO MD : PEPCO NC : Dominion VA : Dominion
ENCLOSURE	NEMA 3R
INTERRUPT RATING	65 kAIC
MAIN CIRCUIT BREAKER	NGS
NUMBER OF WIRES	4
WIRE SIZE	(4) #4/0 AWG-500 kcmil

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Metering Products, Volume 1 Tab 4</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 3MCB1000R</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

