

Eaton 3MCB1000R

Catalog Number: 3MCB1000R

Eaton main circuit breaker, 1000A, Aluminum, NEMA 3R, Overhead/underground, 65 kAIC, NGS, Four-wire, Three-phase, 120/208V, (4) #4/0 AWG-500 kcmil



General specifications

Product Name

Eaton main circuit breaker

Catalog Number

3MCB1000R

UPC

782116008278

Product Length/Depth

13.8 in

Product Height

39.4 in

Product Width

27 in

Product Weight

160 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

Catalog Notes

Neutral lugs order 1MCB1200NLK. Main devices with a rating greater than 800A can be used with 800A residential modular stacks, but only as a center fed main.

Product specifications

Amperage Rating

1000 A

Bus material

Aluminum

Feed type

Top/bottom

Phase

Three-phase

Voltage rating

120/208 V

Utility approvals

MI : DTE Energy (Detroit Edison)

MD : Baltimore Gas and Electric

DC : PEPCO

MD : PEPCO

NC : Dominion

VA : Dominion

Enclosure

NEMA 3R

Interrupt rating

65 kAIC

Main circuit breaker

NGS

Number of wires

4

Wire size

(4) #4/0 AWG-500 kcmil

Resources

Brochures

Specifications and datasheets

[Eaton Specification Sheet - 3MCB1000R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)