

# Metal Raceway HBL2400 and HBL2400D Series



Metal Raceway, Device Boxes, Elbows and Tees



| HBL2400 Series | Description   | Color | Catalog Number  |
|----------------|---|-------|---|
|                | <b>Undivided Base and Cover</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths. | Ivory | <b>HBL2400BCIV</b><br>A: 60.00" (1,524.00)<br>B: 1.91" (48.51)<br>C: .88" (22.40) |





| HBL2400 Series<br>Base and Cover | Description   | Color | Catalog Number   | HBL2400D Series<br>Base and Cover | Description  | Color | Catalog Number  |
|----------------------------------|---|-------|--|-----------------------------------|--|-------|---|
|                                  | <b>10 Ft. Base, Undivided</b><br>Packed 100 ft. (30.5m) per carton,<br>10 ft. (3m) lengths. | Ivory | <b>HBL2400B10IV</b><br>A: 120.00" (3,048.00)<br>B: 1.91" (48.51) |                                   | <b>5 Ft. Cover</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths. | Ivory | <b>HBL2400CIV</b><br>A: 60.00" (1,524.00)<br>B: 1.89" (48.00) |
|                                  | <b>5 Ft. Base, Undivided</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths.    | Ivory | <b>HBL2400BIV</b><br>A: 60.00" (1,524.00)<br>B: 1.91" (48.51)    |                                   |  |       |   |
|                                  | <b>10 Ft. Base, Divided</b><br>Packed 100 ft. (30.5m) per carton,<br>10 ft. (3m) lengths.   | Ivory | <b>HBL2400BDIV</b><br>A: 120.00" (3,048.00)<br>B: 1.91" (48.51)  |                                   |  |       |   |



| Standard | Extra Deep | Description   | Color          | Type                 | 1-Gang   | 2-Gang   |
|----------|------------|---|----------------|----------------------|--|--|
|          |            | <b>Device Box</b><br>For deep switches and receptacles. Base has<br>one 1/2 in. trade size KO and rectangular KO for<br>extension to wall box.                          | Ivory<br>Ivory | Divided<br>Undivided | —<br><b>HBL2448IV</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.75" (44.45)                 | —<br><b>HBL24482IV</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.75" (44.45)                   |
|          |            | <b>Device Box</b><br>For deep switches and receptacles. Base has<br>one 1/2 in. trade size KO and rectangular KO for<br>extension to wall box (undivided box pictured). | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2444DIV</b><br><b>HBL2444IV</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 2.75" (69.85) | <b>HBL2444D2AIV</b><br><b>HBL24442IV</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 2.75" (69.85) |

| Elbows and Tees | Description  | Color          | Type                 | Catalog Number  | Description  | Color          | Type                 | Catalog Number   |
|-----------------|--|----------------|----------------------|---|--|----------------|----------------------|--|
|                 | <b>Internal Elbow Bend Radius</b><br>For inside surfaces at right<br>angles, requiring a 1.5 in.<br>(38.10) bend radius. Suitable<br>for Category 5, 5e, 6<br>and 6a applications. | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2417DFOIV*</b><br><b>HBL2417IV**</b><br>A: 1.91" (48.51)<br>B: 3.60" (91.30)                      | <b>External Elbow Bend Radius</b><br>For right angle turns around<br>external corners. Suitable for<br>Category 5, 5e, 6 and 6a<br>applications. | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2418DFOIV*</b><br><b>HBL2418IV**</b><br>A: 1.91" (48.51)<br>B: 3.83" (97.28)                       |
|                 | <b>90° Flat Elbow Bend Radius</b><br>For right angle turns on<br>same surface. Suitable for<br>Category 5, 5e, 6 and 6a<br>applications.   | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2411DFOIV*</b><br><b>HBL2411IV**</b><br>A: 6.00" (152.40)<br>B: 5.00" (127.00)<br>C: .90" (22.86) | <b>Tee Fitting Bend Radius</b><br>For branches at right angles.<br>Suitable for Category 5, 5e,<br>6 and 6a applications.                        | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2415DFOIV*</b><br><b>HBL2415IV**</b><br>A: 7.30" (185.42)<br>B: 4.99" (126.75)<br>C: 1.44" (36.58) |



Note: \* HBL2401DC couplings included.  
\*\* HBL2401C couplings included.

# Metal Raceway

## HBL2400 and HBL2400D Series






Metal Raceway, Device Boxes, Elbows and Tees



| HBL2400 Series | Description   | Color | Catalog Number  |
|----------------|---|-------|---|
|                | <b>Undivided Base and Cover</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths. | Ivory | <b>HBL2400BCIV</b><br>A: 60.00" (1,524.00)<br>B: 1.91" (48.51)<br>C: .88" (22.40) |





| HBL2400 Series Base and Cover | Description   | Color | Catalog Number   | HBL2400D Series Base and Cover | Description  | Color | Catalog Number  |
|-------------------------------|---|-------|--|--------------------------------|--|-------|---|
|                               | <b>10 Ft. Base, Undivided</b><br>Packed 100 ft. (30.5m) per carton,<br>10 ft. (3m) lengths. | Ivory | <b>HBL2400B10IV</b><br>A: 120.00" (3,048.00)<br>B: 1.91" (48.51) |                                | <b>5 Ft. Cover</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths. | Ivory | <b>HBL2400CIV</b><br>A: 60.00" (1,524.00)<br>B: 1.89" (48.00) |
|                               | <b>5 Ft. Base, Undivided</b><br>Packed 50 ft. (15m) per carton,<br>5 ft. (1.5m) lengths.    | Ivory | <b>HBL2400BIV</b><br>A: 60.00" (1,524.00)<br>B: 1.91" (48.51)    |                                |  |       |   |
|                               | <b>10 Ft. Base, Divided</b><br>Packed 100 ft. (30.5m) per carton,<br>10 ft. (3m) lengths.   | Ivory | <b>HBL2400BDIV</b><br>A: 120.00" (3,048.00)<br>B: 1.91" (48.51)  |                                |  |       |   |



| Standard | Extra Deep | Description   | Color          | Type                 | 1-Gang   | 2-Gang   |
|----------|------------|---|----------------|----------------------|--|--|
|          |            | <b>Device Box</b><br>For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box.                          | Ivory<br>Ivory | Divided<br>Undivided | —<br><b>HBL2448IV</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 1.75" (44.45)                 | —<br><b>HBL24482IV</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 1.75" (44.45)                   |
|          |            | <b>Device Box</b><br>For deep switches and receptacles. Base has one 1/2 in. trade size KO and rectangular KO for extension to wall box (undivided box pictured). | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2444DIV</b><br><b>HBL2444IV</b><br>A: 4.54" (115.32)<br>B: 2.82" (71.63)<br>C: 2.75" (69.85) | <b>HBL2444D2AIV</b><br><b>HBL24442IV</b><br>A: 4.54" (115.32)<br>B: 4.64" (117.86)<br>C: 2.75" (69.85) |

| Elbows and Tees | Description  | Color          | Type                 | Catalog Number  | Description   | Color          | Type                 | Catalog Number   |
|-----------------|--|----------------|----------------------|---|---|----------------|----------------------|--|
|                 | <b>Internal Elbow Bend Radius</b><br>For inside surfaces at right angles, requiring a 1.5 in. (38.10) bend radius. Suitable for Category 5, 5e, 6 and 6a applications. | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2417DFOIV*</b><br><b>HBL2417IV**</b><br>A: 1.91" (48.51)<br>B: 3.60" (91.30)                      | <b>External Elbow Bend Radius</b><br>For right angle turns around external corners. Suitable for Category 5, 5e, 6 and 6a applications. | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2418DFOIV*</b><br><b>HBL2418IV**</b><br>A: 1.91" (48.51)<br>B: 3.83" (97.28)                       |
|                 | <b>90° Flat Elbow Bend Radius</b><br>For right angle turns on same surface. Suitable for Category 5, 5e, 6 and 6a applications.  | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2411DFOIV*</b><br><b>HBL2411IV**</b><br>A: 6.00" (152.40)<br>B: 5.00" (127.00)<br>C: .90" (22.86) | <b>Tee Fitting Bend Radius</b><br>For branches at right angles. Suitable for Category 5, 5e, 6 and 6a applications.                     | Ivory<br>Ivory | Divided<br>Undivided | <b>HBL2415DFOIV*</b><br><b>HBL2415IV**</b><br>A: 7.30" (185.42)<br>B: 4.99" (126.75)<br>C: 1.44" (36.58) |



Note: \* HBL2401DC couplings included.  
\*\* HBL2401C couplings included.

