



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



407DC12 1/2" Ins Diecast Squeeze Connector

Bridgeport Fittings

Catalog Number	407DC12
Manufacturer	Bridgeport Fittings
Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1/2 Inch
Weight per unit	0.0900 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	180 Deg
Connector Type	Squeeze, Insulated
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1/2
------	-----

Descriptions

Description	1/2" INS DIECAST SQUEEZE CONNECTOR
extra long description	BPT 407-DC12 1/2" SQUEEZE CONN.
Long Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1/2 Inch
Product Type	1/2" Squeeze Conn.

Manufacturer Information

Brand	Bridgeport
GTIN	00781747164070
Manufacturers Part Number	407-DC12
UPC	781747164070

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1/2
------------	-----

Packaging

Carton	50
Package	200
Weight Per each	0.09



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Recommended cable types to connect steel flexible metal conduit or armored cable to box or enclosure. Insulator rated 105 degree C. Armored Cable .86" - .92 DIA.

standard

UL

Temperature Rating

105°C