



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 40BC25PK120 \*Delisted\* 40W 120V B10 BLNT Tip CND Base CLR Incan *Ge By Current Lamps*

Catalog Number	40BC25PK120
Manufacturer	Ge By Current Lamps
Description	Decorative Incandescent Lamp, 2500 K, 370 LM Brightness (Lumens), 40 W, 120 V, Clear, CC-2V Filament, 1500 H Average Life, Candelabra Base, Non Dimmable, 1.25 In Diameter, 3.75 In Length, 0.05 LB
Weight per unit	0.0500 (lbs/each)
Product Category	Incandescent Decorative B, C, Ca

### Features

Base	Candelabra Screw (E12)
lumens	370.0
Voltage Rating	120.0
Wattage	40.0

### Material, Color, and Finish

Color	Clear
Finish	Clear

### Dimensions and Weight

Diameter	1.25
----------	------

### Descriptions

Description	*DELISTED*40W 120V B10 BLNT TIP CND BASE CLR INCAN
extra long description	GEL 40BC-25PK-120 15788 INCANDESC

### Manufacturer Information

Brand	GE Current
GTIN	00043168157889
Manufacturers Part Number	40BC-25PK-120
UPC	043168157889

### Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
----------------------	--------------

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Package	25
Weight Per each	0.05