



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



40BC25PK120 *Delisted* 40W 120V B10 BLNT Tip CND Base CLR Incan *Ge By Current Lamps*

Catalog Number	40BC25PK120
Manufacturer	Ge By Current Lamps
Description	Decorative Incandescent Lamp, 2500 K, 370 LM Brightness (Lumens), 40 W, 120 V, Clear, CC-2V Filament, 1500 H Average Life, Candelabra Base, Non Dimmable, 1.25 In Diameter, 3.75 In Length, 0.05 LB
Weight per unit	0.0500 (lbs/each)
Product Category	Incandescent Decorative B, C, Ca

Features

Base	Candelabra Screw (E12)
lumens	370
Voltage Rating	120
Wattage	40

Material, Color, and Finish

Color	Colorless
Finish	Clear

Dimensions and Weight

Diameter	1.25
----------	------

Descriptions

Description	*DELISTED*40W 120V B10 BLNT TIP CND BASE CLR INCAN
-------------	--

Manufacturer Information

Brand	GE Current
GTIN	00043168157889
Manufacturers Part Number	40BC-25PK-120
UPC	043168157889

Taxonomies, Classifications, and Categories

Category Description	INCANDESCENT
----------------------	--------------

Availability

Manufacturer Status	Inactive
Status	Inactive

Packaging

Carton	1
Package	25
Weight Per each	0.05