



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



412DCI2 1-1/4" Ins Diecast Squeeze Connector *Bridgeport Fittings*

Catalog Number	412DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1 1/4 Inch
Weight per unit	0.3270 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	180 Deg
Connector Type	Squeeze, Insulated
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1-1/4
------	-------

Descriptions

Description	1-1/4" INS DIECAST SQUEEZE CONNECTOR
extra long description	BPT 412-DCI2 1 1/4" SQUEEZE CONN. I
Long Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1 1/4 Inch
Product Type	1 1/4" Squeeze Conn. Ins. Zinc
Special Features	Furnished with Tri-Drive screw

Manufacturer Information

Brand	Bridgeport
GTIN	00781747164124
Manufacturers Part Number	412-DCI2
UPC	781747164124

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1-1/4
------------	-------

Packaging

Carton	10
Package	100
Weight Per each	0.327



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Used to connect steel flexible metal conduit to box or enclosure.
standard	Insulator rated 105 degree C.
Temperature Rating	UL
	105°C