



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



414DCI2 1-1/2" Ins Diecast Squeeze Connector

Bridgeport Fittings

Catalog Number	414DCI2
Manufacturer	Bridgeport Fittings
Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1 1/2 Inch
Weight per unit	0.4000 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	180 Deg
Connector Type	Squeeze, Insulated
Material	Zinc Die Cast
media	Yes

Material, Color, and Finish

Finish	Ball burnish
--------	--------------

Dimensions and Weight

Size	1-1/2
------	-------

Descriptions

Description	1-1/2" INS DIECAST SQUEEZE CONNECTOR
extra long description	BPT 414-DCI2 1 1/2" SQUEEZE CONN. I
Long Description	Connector, Squeeze, Zinc Die Cast, Insulated Throat, Trade Size 1 1/2 Inch
Product Type	1 1/2" Squeeze Conn. Ins. Zinc
Special Features	Furnished with Tri-Drive screw

Manufacturer Information

Brand	Bridgeport
GTIN	00781747164148
Manufacturers Part Number	414-DCI2
UPC	781747164148

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	CONNECTOR

Trade Size

Trade Size	1-1/2
------------	-------

Packaging

Carton	5
Package	50
Weight Per each	0.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Used to connect flexible metal conduit or armored cable to box or enclosure. Insulator rated 105 degree C.
standard	UL
Temperature Rating	105°C