Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

41587 15W Led T8 48" 41K DBL 120-277V 2200LM

Sylvania-Ledvance

Catalog Number	41587
Manufacturer	Sylvania-Ledvance
Description	4FT, Ledlescenttm Ballast Free Dimmable Led T8, Frosted Glass, 15W, 120 277V, 82 Cri, 2200 Lumens, 4100 K, 50000 HRS Life.
Weight per unit	0.4800 (lbs/each)
Product Category	Lighting

Features

lumens	2,200
Voltage	120.00 - 277.00 V

Descriptions

Description	15W LED T8 48" 41K DBL 120-277V 2200LM
extra long description	LDV LED15T8L48FGDIM841BFG2/41587 LE
Long Description	4ft, LEDlescentTM Ballast Free Dimmable LED T8, frosted glass, 15W, 120 277V, 82 CRI, 2200 Lumens, 4100 K, 50000 hrs Life.
Product Type	LED15T8L48FGDIM841BFG2 25/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135415876
Manufacturers Part Number	LED15T8L48FGDIM841BF/41587
UPC	046135415876

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS

Packaging

Carton	25
Weight Per each	0.48