



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 41875 8' 42W Led T8 50K DBL End FA8/R17D 2 4' Sections *Sylvania-Ledvance*

Catalog Number	41875
Manufacturer	Sylvania-Ledvance
Description	8FT Ledlescent Direct Wire Ballast Free Type B Led T8, Glass With Frosted Shatter Resistant Pet Coating, 42W, 120 277V, 80 Cri, 5000 Lumens, 5000K, 50000 HRS Life. 2 PC Snap Fit Design. Changeable Single Pin and RDC Base, Dimmable
Weight per unit	0.8820 (lbs/each)
Product Category	Lighting

### Features

lumens	5,040
Voltage	120.00 - 277.00 V

### Descriptions

Description	8' 42W LED T8 50K DBL END FA8/R17D 2 4' SECTIONS
extra long description	SYL LED42T8HOL96-2FGPDIM850BF/41875
Long Description	8ft LEDlescent Direct Wire Ballast Free Type B LED T8, Glass with frosted shatter resistant PET coating, 42W, 120 277V, 80 CRI, 5000 Lumens, 5000K, 50000 Hrs life. 2 pc Snap Fit design. Changeable single pin and RDC base, dimmable
Product Type	LED42T8HOL96 2FGPDIM850BF 10/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135418754
Manufacturers Part Number	LED42T8HOL96-2FGP850BF/41875
UPC	046135418754

### Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

### Packaging

Carton	1
Package	10
Weight Per each	0.882