



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IMAGE
COMING
SOON

41991 24W Led T5 Ho 48" 41K DBL End Line Voltage 3500LM

Sylvania-Ledvance

Catalog Number	41991
Manufacturer	Sylvania-Ledvance
Description	4FT, Ledlescent Ballast Free Led T5HO, Frosted Glass, 24W, 120 277V, 82 Cri, 3500 Lumens, 4100 K, 50000 HRS Life
Weight per unit	0.3090 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED T5HO LEDLESCENT 4FT
lumens	3,500
Voltage	120.00 - 277.00 V

Descriptions

Description	24W LED T5 HO 48" 41K DBL END LINE VOLTAGE 3500LM
extra long description	SYL LED24T5HOL48FGDIM841BFG2/41991
Long Description	4ft, LEDlescent Ballast Free LED T5HO, Frosted glass, 24W, 120 277V, 82 CRI, 3500 Lumens, 4100 K, 50000 hrs Life
Product Type	LED24T5HOL48FGDIM841BFG2 25/CS 1/Sku

Manufacturer Information

Brand	Ledvance
GTIN	00046135419911
Manufacturers Part Number	LED24T5HOL48FGDIM841BFG2/41991
UPC	046135419911

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	---

Packaging

Carton	1
Package	25
Weight Per each	0.309