



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



44102 Wire Marker BKLT, Asst A-Z, 0-15, +, -, /, 10 Each

Ideal

| | |
|------------------|--|
| Catalog Number | 44102 |
| Manufacturer | Ideal |
| Description | Ideal, Wire Marker Booklet, Size: 1/4 X 1-1/2 In Marker, Material: Plastic-Impregnated Cloth, Legend: A-Z, 0-15, +, -, /, Temperature Rating: -40 to 180 Deg F, Markers Per Page: 10, Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 Oz/In Width Ultimate, Includes: 450 Wire Markers and 450 Terminal Markers |
| Weight per unit | 0.1400 (lbs/each) |
| Product Category | Markers & Marking Tapes |

Features

| | |
|-----------------|---------------------------|
| Legend | A-Z, 0-15, +, -, / |
| Material | Plastic-Impregnated Cloth |
| Number of Pages | 10/Booklet |

Material, Color, and Finish

| | |
|--------------|-----------------|
| Legend Color | Non-Smear Black |
|--------------|-----------------|

Dimensions and Weight

| | |
|------|-----------------------|
| Size | 1/4 X 1-1/2 IN Marker |
|------|-----------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | WIRE MARKER BKLT, ASST A-Z, 0-15, +, -, /, 10 EACH |
| extra long description | IDEAL 44-102 Wire Marker Booklet,Id |
| Features | Convenient pocket-size bookletsPlastic, cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilPerforated 1/4 in. x 1-1/2 in. markers can be separated into half-length sizesNon-smear black legendSelf-sticking on wire and cableFor applications above or below groundTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate |
| Long Description | IDEAL, Wire Marker Booklet, Size: 1/4 X 1-1/2 IN Marker, Material: Plastic-Impregnated Cloth, Legend: A-Z, 0-15, +, , /, Temperature Rating: -40 To 180 DEG F, Markers Per Page: 10, Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 OZ/IN Width Ultimate, Includes: 450 Wire Markers And 450 Terminal Markers |
| Product Type | Wire Marker Booklet, Ideal, SZ: 1/4 X 1-1/2 In MRKR, Plastic-Im |
| Special Features | Features: Convenient Pocket-Size Booklets; Plastic-Impregnated Cloth Construction For Long-Lasting Durability; Resists Abrasion, Moisture, Dirt And Oil; Perforated 1-1/2 IN Markers Can Be Separated Into Half-Length Sizes; Self-Sticking On Wire And Cable; Non-Smear Black Legend Ensures High Visibility; For Applications Above Or Below Ground; Ten Pages Per Booklet, 10 Markers Per Legend; Adhesion: 45 OZ/IN Width Ultimate; Includes: 450 Wire Markers And 450 Terminal Markers |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250441020 |
| Manufacturers Part Number | 44-102 |
| UPC | 783250441020 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | WIRE LUBE, MARKERS, & TIES |
|----------------------|----------------------------|

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Weight Per each | 0.14 |

Uses, Certifications, and Standards

| | |
|--------------------|------------|
| standard | RoHS |
| Temperature Rating | -40 To 180 |