



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



44808 Adjustable Cable Lockout

Ideal

Catalog Number	44808
Manufacturer	Ideal
Description	Ideal, Cable Lockout, Adjustable, Material: Steel Cable, Thermoplastic Body, Insulation: Insulated, Size: 1/4 In, Length: 6 FT, Finish: Clear Vinyl Coating, Cable Type: Flexible Multi-Stranded
Weight per unit	0.6000 (lbs/each)
Product Category	Safety Equipment

Features

insulation	Insulated
Material	Steel Cable, Thermoplastic Body

Dimensions and Weight

Length	6
Size	1/4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	ADJUSTABLE CABLE LOCKOUT
extra long description	IDEAL 44-808 ADJUSTABLE CABLE LOCKO
Features	Infinitely adjustable safety hasp and cable ideal for multiple circuit breaker panels and side-by-side gate valve lockouts Feed the cable end through the points to be locked out, then back through the lockout body. Cinch it tight to remove any slack with the patented locking feature. Tough, flexible multi-stranded 6 ft. 1/4 in. dia. steel cable is insulated with a clear vinyl coating Tough, lightweight, dielectric thermoplastic body withstands chemicals; performs effectively in extreme conditions Up to four wor
Long Description	IDEAL, Cable Lockout, Adjustable, Material: Steel Cable, Thermoplastic Body, Insulation: insulated, Size: 1/4 IN, Length: 6 FT, Finish: Clear Vinyl Coating, Cable Type: Flexible Multi-Stranded
Product Type	Adjustable Cable Lockout
Special Features	Features: Infinitely Adjustable Safety Hasp And Cable; Ideal For Multiple Circuit Breaker Panels And Side-By-Side Gate Valve Lockouts; Feed The Cable End Through The Points To Be Locked Out, Then Back Through The Lockout Body. Cinch It Tight To Remove Any Slack With The Patented Locking Feature; Tough, Flexible Multi-Stranded 6 FT 1/4 IN Dia. Steel Cable Is Insulated With A Clear Vinyl Coating; Tough, Lightweight, Dielectric Xenoy® Thermoplastic Body Withstands Chemicals; Performs Effectively In Extreme Co

Manufacturer Information

Brand	Ideal
GTIN	00783250448081
Manufacturers Part Number	44-808
UPC	783250448081

Taxonomies, Classifications, and Categories

Category Description	SAFETY PRODUCTS
Type	ADJUSTABLE

Packaging

Carton	1
Weight Per each	0.6

Uses, Certifications, and Standards

standard	RoHS
----------	------