

HOUSING


Dimensions	Length	Width	Height	Cutout
Standard Housing	11-1/8"	13-5/8"	H"	5-1/8"
Chicago Plenum	11-1/8"	13-5/8"	H"	

Height varies with socket position; see reflector line drawing below for overall fixture height. Add 1/2" height for Chicago Plenum option.

4" Non-Ferrous Downlight

A19
PAR16/20
R20

Non-ferrous downlight for MRI suites. Medium and wide beam distribution for general and task lighting from a variety of vertically mounted incandescent and halogen lamps. Adjustable socket position maintains focus for varied reflector types. Rated for DC operation.



HOUSING

HD4MRI=Non-Ferrous Incandescent


HD4MRICP=Non-Ferrous Incandescent, Chicago Plenum

ACCESSORIES

TRR4=Rimless Trim Ring, White*

*Not compatible with Self Flange

TRIM



TRIM

4501=Self Flanged

FINISH


LI=Low Iridescent Clear
H=Haze
WMH=Warm Haze
G=Gold
WH=Wheat
B=Black
W=Gloss White
GP=Graphite
GPH=Graphite Haze
K=Cognac
KH=Cognac Haze

OPTIONS

WF=White
Painted
Flange (Self
Flanged only)
DR=Derated
Wattage
Label

Open Downlight

A19 100W Max (Medium Beam)



TRIM

4551=Self Flanged
4550=Molded Trim Ring, White

FINISH


LI=Low Iridescent Clear
H=Haze
WMH=Warm Haze
G=Gold
WH=Wheat
B=Black
W=Gloss White
GP=Graphite
GPH=Graphite Haze
K=Cognac
KH=Cognac Haze

OPTIONS

WF=White
Painted
Flange (Self
Flanged only)
DR=Derated
Wattage
Label

Open Downlight

A19 100W Max (Wide Beam)



TRIM

4511=Single Wall Wash, Self Flanged
4510=Single Wall Wash, Molded Trim Ring, White
4521=Double Wall Wash, Self Flanged
4520=Double Wall Wash, Molded Trim Ring, White
4531=Corner Wall Wash, Self Flanged
4530=Corner Wall Wash, Molded Trim Ring, White

FINISH


LI=Low Iridescent Clear
H=Haze
WMH=Warm Haze
G=Gold
WH=Wheat
B=Black
W=Gloss White
GP=Graphite
GPH=Graphite Haze
K=Cognac
KH=Cognac Haze

OPTIONS

WF=White
Painted
Flange (Self
Flanged only)
DR=Derated
Wattage
Label

Open Wall Wash

GRUVI
A19 100W Max



TRIM

4201=Self Flanged
4200=Molded Trim Ring, White

FINISH

LI=Low Iridescent Clear
H=Haze
WMH=Warm Haze
G=Gold
WH=Wheat
B=Black
W=Gloss White
GP=Graphite
GPH=Graphite Haze
K=Cognac
KH=Cognac Haze
BB=Black Baffle
(4200 only)
WB=White Baffle
(4200 only)

OPTIONS

WF=White
Painted
Flange (Self
Flanged only)
DR=Derated
Wattage
Label

Open Downlight

PAR16/20 60W Max
R20 60W Max



Ordering Example

Housing, Trim, Accessories and Lamps ordered as separate line items.

Housing	Trim	Accessories
HD4MRI	4501LI	TRR4