
46746

F32T8 TL941/ALTO (PK30)



Application: Industrial, Food Processing, Food Service,
Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Color Temperature: 4100K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 2470

Package Weight: 15.40 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Average Life Hours: 36000

Bulb: T8

Color: TL941

CRI: 90

Initial Lumens: 2600

Length: 48.00 IN

Package (LxWxH): 49.80 IN x 6.50 IN x 7.90 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585070084

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone

46746

F32T8 TL941/ALTO (PK30)



Application: Industrial, Food Processing, Food Service,
Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Color Temperature: 4100K

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 2470

Package Weight: 15.40 L

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Average Life Hours: 36000

Bulb: T8

Color: TL941

CRI: 90

Initial Lumens: 2600

Length: 48.00 IN

Package (LxWxH): 49.80 IN x 6.50 IN x 7.90 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585070084

ULEPH,UL 2007A,ROHS,NSF Non-Food Zone,NSF Splash Zone