



Cut Level 3 Dipped Gloves

Milwaukee Tool's cut resistant dipped gloves are designed to provide ultimate durability, all-day comfort, and best in class dexterity for handling small objects. These gloves feature ANSI and EN cut level III protection as well as best in class puncture resistance to help prevent injuries from sharp objects on the jobsite. Additionally, Milwaukee cut resistant gloves utilize a Comfort Web Grip to provide all-day comfort, best in class grip performance, and ultimate durability. SMARTSWIPE™ fingertips & palms provide full access to touchscreen devices without removing the gloves and also feature high dexterity fingertips to maximize control when handling small objects.

INCLUDES:

(1) Pair Cut Level 3 Dipped Gloves

FEATURES:

- ANSI & EN cut rating 3
- Comfort Web Grip for best in class grip performance and comfortable fit
- SMARTSWIPE™ palm and fingertips permits the use of touch screen devices without removing gloves
- Best in class puncture rating for resistance to sharp materials
- High dexterity design when handling small objects
- Nylon & HPPE liner material
- TDM cut rating C
- Abrasion rating 4
- Tear rating 4
- Puncture rating 3
- Breathable glove design
- Ideal use for demolition, wire-stripping, and pipe threading applications

PRODUCT SPECIFICATIONS:

Item/Size Information:

48-22-8930 – Small 48-22-8931 – Medium 48-22-8932 – Large
 48-22-8933 – XL 48-22-8934 - XXL

| | |
|--------|--------------------------------------|
| Width | 5.25" |
| Weight | 0.18 lbs |
| Washer | Regular cycle, Warm wash, Cool rinse |

| | |
|--------|----------------------|
| Dryer | Tumble dry, Low heat |
| Height | 0.25" |
| Length | 8.75" |



Cut Level 3 Dipped Gloves

Milwaukee Tool's cut resistant dipped gloves are designed to provide ultimate durability, all-day comfort, and best in class dexterity for handling small objects. These gloves feature ANSI and EN cut level III protection as well as best in class puncture resistance to help prevent injuries from sharp objects on the jobsite. Additionally, Milwaukee cut resistant gloves utilize a Comfort Web Grip to provide all-day comfort, best in class grip performance, and ultimate durability. SMARTSWIPE™ fingertips & palms provide full access to touchscreen devices without removing the gloves and also feature high dexterity fingertips to maximize control when handling small objects.

INCLUDES:

(1) Pair Cut Level 3 Dipped Gloves

FEATURES:

- ANSI & EN cut rating 3
- Comfort Web Grip for best in class grip performance and comfortable fit
- SMARTSWIPE™ palm and fingertips permits the use of touch screen devices without removing gloves
- Best in class puncture rating for resistance to sharp materials
- High dexterity design when handling small objects
- Nylon & HPPE liner material
- TDM cut rating C
- Abrasion rating 4
- Tear rating 4
- Puncture rating 3
- Breathable glove design
- Ideal use for demolition, wire-stripping, and pipe threading applications

PRODUCT SPECIFICATIONS:

Item/Size Information:

48-22-8930 – Small

48-22-8931 – Medium

48-22-8932 – Large

48-22-8933 – XL

48-22-8934 - XXL

| | |
|--------|--------------------------------------|
| Width | 5.25" |
| Weight | 0.18 lbs |
| Washer | Regular cycle, Warm wash, Cool rinse |

| | |
|--------|----------------------|
| Dryer | Tumble dry, Low heat |
| Height | 0.25" |
| Length | 8.75" |