



**M18 REDLITHIUM™**  
**THE WORLD'S FIRST & ONLY 18V**  
**HIGH DEMAND™ 9.0 BATTERY**

[Learn More](#)

Swap Banner



## 9-3/4" Ground Rod Driver

48-62-4091

### What's Included

(1) 9-3/4" Ground Rod Driver (48-62-4091)

### Where to Buy



Shop Online



Find Local



### Features

- Ground Rod Driver
- SDS-Max Shank
- 9-3/4" L x 5/8" x 3/4" Rod Dia
- Made from forged high grade steel

### Specifications

Type	Carbide Bits Masonry Drill Bits
Size	9810 and 1-2 L - 5-8 Inch and 3-4 Inch Rod Dia
Width	5/8" & 3/4" Rods
Length	9-3/4"
Pack Qty	1 Pack
Style	Ground Rod Driver

### Overview

Drives soft ground rods. Socket depth - 2-3/4", inner diameter - .906. Rod Diameter 5/8" and 3/4", Length 10"

### Model Options

Item/Cat #	
48-62-4063	<p><a href="#">Shop Online</a></p> <p><a href="#">Find Local</a></p>

Item/Cat #	
48-62-4065	Shop Online Find Local
48-62-3060	Shop Online Find Local
48-62-4066	Shop Online Find Local
48-62-4068	Shop Online Find Local
48-62-4073	Shop Online Find Local
48-62-4075	Shop Online Find Local
48-62-4077	Shop Online Find Local
48-62-4079	Shop Online Find Local
48-62-4080	Shop Online Find Local
48-62-4081	Shop Online Find Local
48-62-4082	Shop Online Find Local
48-62-4085	Shop Online Find Local
48-62-4087	Shop Online Find Local
48-62-4089	Shop Online Find Local
48-62-4091	Shop Online Find Local
48-62-4092	Shop Online Find Local
48-62-4168	Shop Online Find Local
48-62-4175	Shop Online Find Local

Item/Cat #	
48-62-4177	Shop Online Find Local
48-62-4179	Shop Online Find Local
48-62-4181	Shop Online Find Local
48-62-4185	Shop Online Find Local
48-62-4187	Shop Online Find Local



**M18 REDLITHIUM™**  
**THE WORLD'S FIRST & ONLY 18V**  
**HIGH DEMAND™ 9.0 BATTERY**

[Learn More](#)

Swap Banner



## 9-3/4" Ground Rod Driver

48-62-4091

### What's Included

(1) 9-3/4" Ground Rod Driver (48-62-4091)

### Where to Buy



Shop Online



Find Local



### Features

- Ground Rod Driver
- SDS-Max Shank
- 9-3/4" L x 5/8" x 3/4" Rod Dia
- Made from forged high grade steel

### Specifications

<b>Type</b>	Carbide Bits Masonry Drill Bits
<b>Size</b>	9810 and 1-2 L - 5-8 Inch and 3-4 Inch Rod Dia
<b>Width</b>	5/8" & 3/4" Rods
<b>Length</b>	9-3/4"
<b>Pack Qty</b>	1 Pack
<b>Style</b>	Ground Rod Driver

### Overview

Drives soft ground rods. Socket depth - 2-3/4", inner diameter - .906. Rod Diameter 5/8" and 3/4", Length 10"

### Model Options

<b>Item/Cat #</b>	
48-62-4063	<p><a href="#">Shop Online</a></p> <p><a href="#">Find Local</a></p>

Item/Cat #	
48-62-4065	Shop Online Find Local
48-62-3060	Shop Online Find Local
48-62-4066	Shop Online Find Local
48-62-4068	Shop Online Find Local
48-62-4073	Shop Online Find Local
48-62-4075	Shop Online Find Local
48-62-4077	Shop Online Find Local
48-62-4079	Shop Online Find Local
48-62-4080	Shop Online Find Local
48-62-4081	Shop Online Find Local
48-62-4082	Shop Online Find Local
48-62-4085	Shop Online Find Local
48-62-4087	Shop Online Find Local
48-62-4089	Shop Online Find Local
48-62-4091	Shop Online Find Local
48-62-4092	Shop Online Find Local
48-62-4168	Shop Online Find Local
48-62-4175	Shop Online Find Local

Item/Cat #	
48-62-4177	Shop Online Find Local
48-62-4179	Shop Online Find Local
48-62-4181	Shop Online Find Local
48-62-4185	Shop Online Find Local
48-62-4187	Shop Online Find Local