



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 4887 Conn 15A 125V 2P3W Vinyl STR YI

*Eaton Wiring Devices*

Catalog Number	4887
Manufacturer	Eaton Wiring Devices
Description	15A/125V Nema 5-15R Yellow Vinyl Straight Blade Cord Conn, Cooper 4887
Weight per unit	0.1600 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	15
core	5-15R
dimensions	2.6000 IN X 1.5000 IN X 1.5000 IN
Material	Vinyl
Resistance	-20 to +60 C
Voltage Rating	5 +/-1 mA

### Material, Color, and Finish

Color	Black
Conductor Material	Copper
Insulation Material	PVC
Jacket Material	PVC

### Descriptions

Description	CONN 15A 125V 2P3W VINYL STR YL
extra long description	EWD 4887-BOX Conn 15A 125V 2P3W Vin
Features	Southwire™ 59850000 replacement female extension cord end is a construction-grade device. Tough, vinyl or nylon housing with many built-in features for speed and assembly convenience. With a temperature rating of -20 to 60 degrees Celsius, these 5-15R NEMA replacement connectors are built for the toughest environments.
Long Description	15A/125V NEMA 5-15R YELLOW VINYL STRAIGHT BLADE CORD CONN, COOPER 4887
Product Type	15A/125V Receptacle 5-15R
Special Features	Spec grade plugs & conns

### Manufacturer Information

Brand	Southwire
GTIN	00032664341205
Manufacturers Part Number	4887-BOX
UPC	032664341205

### Taxonomies, Classifications, and Categories

Category Description	Residential cord connectors
Type	Cord Set



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	10
Package	100
Weight	0.15
Weight Per each	0.16

## Uses, Certifications, and Standards

Application	Extension Cord
standard	UL817
Temperature Rating	5-15P