



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 48892710 1/16" Thunderbolt Black Oxide Drill Bit

*Milwaukee Electric Tool*

|                  |   |
|------------------|---|
| Catalog Number   | 48892710  |
| Manufacturer     | Milwaukee Electric Tool   |
| Description      | Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt® Web Features A Thicker Core Than A Standard Drill Bit, Which Provides Ultimate Strength and Protects Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips and Debris Fast to Keep The Bit Cool. A Precision Start, 135 Split Point Tip Starts On Contact to Keep The Bit From Walking For Fast Accurate Holes. Excellent For Drilling On Curved Surfaces, Requir |
| Weight per unit  | 0.0150 (lbs/each)   |
| Product Category | Bits, Parts, Accessories  |

### Features

|                  |        |
|------------------|--------|
| Drill Diameter   | 0.0625 |
| Flute Length     | 4.0    |
| package quantity | 1      |
| Shank Diameter   | 0.25   |

### Material, Color, and Finish

|        |             |
|--------|-------------|
| Finish | Black Oxide |
|--------|-------------|

### Dimensions and Weight

|        |     |
|--------|-----|
| Length | 6.0 |
|--------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 1/16" THUNDERBOLT BLACK OXIDE DRILL BIT  |
| extra long description | MILW 48-89-2710 1/16" Thunderbolt B  |
| Features               | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,   |
| Long Description       | Milwaukee® Thunderbolt® Black Oxide Jobber length drill bits are designed for extreme durability and long life. The Thunderbolt® web features a thicker core than a standard drill bit, which provides ultimate strength and protects against side-load breakage. A specially designed parabolic flute form clears chips and debris fast to keep the bit cool. A precision start, 135 Split Point tip starts on contact to keep the bit from walking for fast accurate holes. Excellent for drilling on curved surfaces, require |
| Product Type           | 1/16" Thunderbolt Black Oxide  |
| Short Description      | 1/16" Thunderbolt Blk Oxide  |
| Special Features       | Thunderbolt Web, Provides Longer Life And Faster Driller Times; Parabolic Flute, Clears Chips Faster; 135 DEG Degree Split Point, Precision Start No Walking; Point Type: Split Point; Flute Type: Parabolic; Drill Point: 135 DEG   |

## Manufacturer Information

|                           |                                     |
|---------------------------|-------------------------------------|
| Brand                     | Milwaukee®                          |
| GTIN                      | 00045242166732                      |
| Manufacturers Part Number | 48-89-2710                          |
| series                    | Milwaukee® Thunderbolt® Black Oxide |
| UPC                       | 045242166732                        |

## Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
|----------------------|-----------------------------|

## Packaging

|                 |       |
|-----------------|-------|
| Carton          | 1     |
| Package         | 550   |
| Weight          | 0.015 |
| Weight Per each | 0.015 |

## Uses, Certifications, and Standards

|             |                     |
|-------------|---------------------|
| Application | For Portable Drills |
|-------------|---------------------|