



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892712 3/32" Thunderbolt Black Oxide Drill Bit

Milwaukee Electric Tool

| | |
|------------------|---|
| Catalog Number | 48892712 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt Web Features A Thicker Core Than A Standard Drill Bit to Provide Ultimate Strength and Protect Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips and Debris Fast to Keep The Bit Cool. The 135° Split Point Tip Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes. Effective For Drilling On Curved Surfaces, Milwaukee Thunderbolt Bla |
| Weight per unit | 0.0200 (lbs/each) |
| Product Category | Bits, Parts, Accessories |

Features

| | |
|------------------|-------|
| Drill Diameter | 0.094 |
| Flute Length | 4.0 |
| package quantity | 1 |
| Shank Diameter | 0.25 |

Material, Color, and Finish

| | |
|--------|-------------|
| Finish | Black Oxide |
|--------|-------------|

Dimensions and Weight

| | |
|--------|-----|
| Length | 6.0 |
|--------|-----|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 3/32" THUNDERBOLT BLACK OXIDE DRILL BIT |
| extra long description | MILW 48-89-2712 3/32" Thunderbolt B |
| Features | MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening, |
| Long Description | Milwaukee® Thunderbolt® Black Oxide jobber length drill bits are designed for extreme durability and long life. The Thunderbolt web features a thicker core than a standard drill bit to provide ultimate strength and protect against side-load breakage. A specially designed parabolic flute form clears chips and debris fast to keep the bit cool. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Effective for drilling on curved surfaces, Milwaukee Thunderbolt Bla |
| Product Type | 3/32" Thunderbolt Black Oxide |
| Special Features | Thunderbolt Web, Provides Longer Life And Faster Driller Times; Parabolic Flute, Clears Chips Faster; 135 DEG Degree Split Point, Precision Start No Walking; Point Type: Split Point; Flute Type: Parabolic; Drill Point: 135 DEG |

Manufacturer Information

| | |
|---------------------------|-------------------------------------|
| Brand | Milwaukee® |
| GTIN | 04524216675686 |
| Manufacturers Part Number | 48-89-2712 |
| series | Milwaukee® Thunderbolt® Black Oxide |
| UPC | 045242166756 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------|
| Category Description | BITS, BLADES, AND HOLE SAWS |
|----------------------|-----------------------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 450 |
| Weight | 0.02 |
| Weight Per each | 0.02 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------|
| Application | For Portable Drills |
|-------------|---------------------|