



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



48892712 3/32" Thunderbolt Black Oxide Drill Bit

Milwaukee Electric Tool

Catalog Number	48892712
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt Web Features A Thicker Core Than A Standard Drill Bit to Provide Ultimate Strength and Protect Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips and Debris Fast to Keep The Bit Cool. The 135° Split Point Tip Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes. Effective For Drilling On Curved Surfaces, Milwaukee Thunderbolt Bla
Weight per unit	0.0200 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Drill Diameter	0.094
Flute Length	4.0
package quantity	1
Shank Diameter	0.25

Material, Color, and Finish

Finish	Black Oxide
--------	-------------

Dimensions and Weight

Length	6.0
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	3/32" THUNDERBOLT BLACK OXIDE DRILL BIT
extra long description	MILW 48-89-2712 3/32" Thunderbolt B
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee® Thunderbolt® Black Oxide jobber length drill bits are designed for extreme durability and long life. The Thunderbolt web features a thicker core than a standard drill bit to provide ultimate strength and protect against side-load breakage. A specially designed parabolic flute form clears chips and debris fast to keep the bit cool. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Effective for drilling on curved surfaces, Milwaukee Thunderbolt Bla
Product Type	3/32" Thunderbolt Black Oxide
Special Features	Thunderbolt Web, Provides Longer Life And Faster Driller Times; Parabolic Flute, Clears Chips Faster; 135 DEG Degree Split Point, Precision Start No Walking; Point Type: Split Point; Flute Type: Parabolic; Drill Point: 135 DEG

Manufacturer Information

Brand	Milwaukee®
GTIN	04524216675686
Manufacturers Part Number	48-89-2712
series	Milwaukee® Thunderbolt® Black Oxide
UPC	045242166756

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Package	450
Weight	0.02
Weight Per each	0.02

Uses, Certifications, and Standards

Application	For Portable Drills
-------------	---------------------