



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

48892717 11/64" Thunderbolt Black Oxide Drill Bit

Milwaukee Electric Tool

Catalog Number	48892717
Manufacturer	Milwaukee Electric Tool
Description	Milwaukee® Thunderbolt® Black Oxide Jobber Length Drill Bits Are Designed For Extreme Durability and Long Life. The Thunderbolt® Web Features A Thicker Core Than A Standard Drill Bit, Which Provides Ultimate Strength and Protects Against Side-Load Breakage. A Specially Designed Parabolic Flute Form Clears Chips and Debris Fast to Keep The Bit Cool. A Precision Start, 135 Split Point Tip Starts On Contact to Keep The Bit From Walking For Fast Accurate Holes. Excellent For Drilling On Curved Surfaces, Requir
Weight per unit	0.0300 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Drill Diameter	0.1720
Flute Length	4.000000
package quantity	1
Shank Diameter	0.250000

Material, Color, and Finish

Finish	Black Oxide
--------	-------------

Dimensions and Weight

Length	6.0
--------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	11/64" THUNDERBOLT BLACK OXIDE DRILL BIT
extra long description	MILW 48-89-2717 11/64" Thunderbolt
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	Milwaukee® Thunderbolt® Black Oxide Jobber length drill bits are designed for extreme durability and long life. The Thunderbolt® web features a thicker core than a standard drill bit, which provides ultimate strength and protects against side-load breakage. A specially designed parabolic flute form clears chips and debris fast to keep the bit cool. A precision start, 135 Split Point tip starts on contact to keep the bit from walking for fast accurate holes. Excellent for drilling on curved surfaces, requir
Product Type	11/64" Thunderbolt Black Oxide
Special Features	Thunderbolt Web, Provides Longer Life And Faster Driller Times; Parabolic Flute, Clears Chips Faster; 135 DEG Degree Split Point, Precision Start No Walking; Point Type: Split Point; Flute Type: Parabolic; Drill Point: 135 DEG

Manufacturer Information

Brand	Milwaukee®
GTIN	04524216684800
Manufacturers Part Number	48-89-2717
series	Milwaukee® Thunderbolt® Black Oxide
UPC	045242166848

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

Packaging

Carton	1
Package	300
Weight	0.030000
Weight Per each	0.03

Uses, Certifications, and Standards

Application	For Portable Drills
-------------	---------------------