



4-Piece SHOCKWAVE™ RED HELIX™ Titanium Drill Bit Set

Milwaukee® SHOCKWAVE Impact Duty Titanium Drill Bits with RED HELIX are engineered for impacts and drills. Designed with a Variable Helix with an aggressive 35° Helix Angle which ends at 15°, the Impact Duty Titanium Drill bits with RED HELIX provide Rapid Chip Removal to limit heat buildup to Stay Sharper Longer. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Titanium coating can be used in all drilling applications to give you up to 3X life vs. Black Oxide Drill Bits.

INCLUDES:

- (1) 1/8 inches (3.2mm)
- (1) 5/32 inches (4.0 mm)
- (1) 3/16 inches (4.8 mm)
- (1) 1/4 inches (6.4 mm)

FEATURES:

- SHOCKWAVE Impact Duty, Engineered for Drills and Impacts
- RED HELIX Design for Rapid Chip Removal
- CHIP BREAKER Decreased Heat Buildup
- 135° split point for precision start no walking

PRODUCT SPECIFICATIONS:

Warranty

Limited Lifetime Warranty



4-Piece SHOCKWAVE™ RED HELIX™ Titanium Drill Bit Set

Milwaukee® SHOCKWAVE Impact Duty Titanium Drill Bits with RED HELIX are engineered for impacts and drills. Designed with a Variable Helix with an aggressive 35° Helix Angle which ends at 15°, the Impact Duty Titanium Drill bits with RED HELIX provide Rapid Chip Removal to limit heat buildup to Stay Sharper Longer. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes. Titanium coating can be used in all drilling applications to give you up to 3X life vs. Black Oxide Drill Bits.

INCLUDES:

- (1) 1/8 inches (3.2mm)
- (1) 5/32 inches (4.0 mm)
- (1) 3/16 inches (4.8 mm)
- (1) 1/4 inches (6.4 mm)

FEATURES:

- SHOCKWAVE Impact Duty, Engineered for Drills and Impacts
- RED HELIX Design for Rapid Chip Removal
- CHIP BREAKER Decreased Heat Buildup
- 135° split point for precision start no walking

PRODUCT SPECIFICATIONS:

Warranty	Limited Lifetime Warranty
----------	---------------------------