



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



49240146 M12 Work Light *Milwaukee Electric Tool*

Catalog Number	49240146
Manufacturer	Milwaukee Electric Tool
Description	The M12™ Cordless Led Work Light Outlasts and Outperforms All Other Subcompact Lights. Powered By An M12™ Red Lithium™ Battery, The Work Light Is 2X Brighter and Whiter Than Conventional Incandescent Bulbs and Runs Up to Twice As Long. With A Sealed Aluminum Head to Provide Impact and Weather Resistance, Milwaukee® Provides A Limited Lifetime Led Warranty. A Magnetic Back Allows Hands-Free Use While A 90 Degree Rotating Head Allows The User to Easily Point The Light Beam At The Desired Work Area.
Weight per unit	0.7300 (lbs/each)
Product Category	Worklight Lighting

Features

battery	Lithium-Ion
Battery Size	Battery Packs
Battery Voltage	12
bulb type	LED
charge time	0.5
lumens	160
Material	Rugged Overmold
Voltage Rating	12
Water Resistant	NO

Material, Color, and Finish

color temperature	5600
-------------------	------

Dimensions and Weight

Size	8.500 IN Length
------	-----------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	M12 WORK LIGHT
extra long description	MILW 49-24-0146 12V LED WORKLIGHT
Features	The M12 series offers solutions that deliver portable productivity. They take on the tightest spaces and are specifically built to go anywhere. They are trade focused, system wide, lightweight with ergonomic design make portability easy, and operation faster and more productive.
Long Description	The M12™ cordless LED work light outlasts and outperforms all other subcompact lights. Powered by an M12™ Red Lithium™ battery, the work light is 2X brighter and whiter than conventional incandescent bulbs and runs up to twice as long. With a sealed aluminum head to provide impact and weather resistance, Milwaukee® provides a limited lifetime LED warranty. A magnetic back allows hands-free use while a 90 degree rotating head allows the user to easily point the light beam at the desired work area.
Product Type	12V Led Worklight
Short Description	12V LED WORKLIGHT
Special Features	Features: Aluminum Head Impact And Weather Resistant; 90 DEG Rotating Head Aims Light At Work Space; Magnetic Back Hands-Free Use; M12 Works With Milwaukee 12 V Redlithium Battery Pack; Tool Weight: 0.900 LB

Manufacturer Information

Brand	Milwaukee®
GTIN	00045242188604
Manufacturers Part Number	49-24-0146
UPC	045242188604

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Cordless, LED

Packaging

Carton	1
Package	8
Weight Per each	0.73