

REDLITHIUM™ 2.0/XC4.0

- Up to 2X More Run-Time
- Up to 20% More Power
- Over 2X More Recharges

M12™ REDLITHIUM™ 2.0 Battery Pack
48-11-2420

Specifications:

Amp Hours	2.0
Cell Chemistry	LITHIUM-ION
Charge Time	45 minutes




M12™ REDLITHIUM™ XC4.0 Battery Pack
48-11-2440

Specifications:

Amp Hours	4.0
Cell Chemistry	LITHIUM-ION
Charge Time	90 minutes



REDLITHIUM™ RUN-TIME ADVANTAGE



M12™ REDLITHIUM™ Compact Battery Pack
48-11-2401

Specifications:

Amp Hours	1.5
Cell Chemistry	LITHIUM-ION
Charge Time	30 minutes



2-Pack Available
48-11-2411

M12™ REDLITHIUM™ XC Extended Capacity Battery Pack
48-11-2402

Specifications:

Amp Hours	3.0
Cell Chemistry	LITHIUM-ION
Charge Time	60 minutes



2-Pack Available
48-11-2412

M12™ Jobsite Radio
2590-20

Specifications:

Tuner	Digital Reception with Signal Processor
Modes	AM/FM/AUX
Weight	3.5 lbs
Auxiliary Input	1/8" Stereo Jack
Powered By	All M12™ Batteries / AC Adapter



Batteries Sold Separately

Includes: (1) Auxiliary Input Cord, (1) AC Adapter, (2) AAA Batteries (for memory backup)

M12™ Power Source
49-24-2310

Specifications:

On-Board Fuel Gauge	Yes
Powered By	All M12™ Batteries
2.1 Amp USB Port	Universal Charging for Smart Phones, Tablets, and Other Portable Electronic Devices



Batteries Sold Separately

Powers all Milwaukee® M12™ Heated Gear



M12™ LITHIUM-ION Battery Charger*
48-59-2401

Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



*Compatible with All M12™ Batteries

M12™ AC/DC Wall & Vehicle Charger*
2510-20

Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



*Compatible with All M12™ Batteries

M12™ and M18™ Multi-Voltage Charger
48-59-1812

Specifications:

Compatibility	All M12™ and M18™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M12™ Heated Jacket Kit - Red
2341 (2340 Jacket-Only)

Specifications:

Heat Zones	5 (Chest, Back, Pockets)
Heat Settings	3 Per Zone (High, Medium, Low)
Jacket Material	100% Polyester
Water / Wind Resistant	Yes
USB Charger	Yes
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) M12™ Power Source, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Jacket Kit - Black
2345 (2344 Jacket-Only)

Specifications:

Heat Zones	5 (Chest, Back, Pockets)
Heat Settings	3 Per Zone (High, Medium, Low)
Jacket Material	100% Polyester
Water / Wind Resistant	Yes
USB Charger	Yes
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) M12™ Power Source, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Jacket Kit Realtree Xtra® Camouflage
2343 (2342 Jacket-Only)

Specifications:

Heat Zones	5 (Chest, Back, Pockets)
Heat Settings	3 Per Zone (High, Medium, Low)
Jacket Material	Soft-Shell Fabric Blend for Reduced Noise During Movement
Water / Wind Resistant	Yes
USB Charger	Yes
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (1) M12™ Power Source, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ High Visibility Heated Jacket Kit
2347 (2346 Jacket-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Jacket Material	ANSI Class III 100% Polyester
Water / Wind Resistant	Yes
Zip-In Removable Hood	Yes
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger

Available Sizes: Medium, Large, XL, 2X, 3X, 4X

M12™ Heated Jacket 12V DC Plug Adapter
49-24-2301



M18™ Power Source
49-24-2371

Batteries Sold Separately

M12™ Heated Hoodie Kit - Red
2371 (2370 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hoodie Material	Cotton/Polyester Blend
Water / Wind Resistant	No
Washer / Dryer Safer	Yes
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Hoodie Kit - Gray
2373 (2372 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hoodie Material	Cotton/Polyester Blend
Water / Wind Resistant	No
Washer / Dryer Safer	Yes
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Hoodie Kit - Khaki
2375 (2374 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hoodie Material	Cotton/Polyester Blend
Water / Wind Resistant	No
Washer / Dryer Safer	Yes
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ High Visibility Heated Hoodie Kit
2377 (2376 Hoodie-Only)

Specifications:

Heat Zones	3 (Chest, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hoodie Material	ANSI Class II 100% Polyester
Water / Wind Resistant	Yes
Washer / Dryer Safer	Yes (Up to 25 Washes)
Run-Time	Up to 6 Hours



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger

Available Sizes: Small, Medium, Large, XL, 2X, 3X

M12™ Heated Hand Warmers

Realtree Xtra® Camouflage 2321-21 (2321-20 Hand Warmer-Only)
Black 2322-21 (2322-20 Hand Warmer-Only)

Specifications:

Heat Zones	2 (Front, Back)
Heat Settings	3 Per Zone (High, Medium, Low)
Hand Warmer Material	100% Polyester
Water / Wind Resistant	Yes
Adjustable Buckle-Strap	Yes



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger

Available Sizes: One Size Fits Most

Realtree Xtra © 2012 of Jordan Outdoor Enterprises, Ltd., all rights reserved