



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

4T 414AWG Du Rated Lug

Nsi Industries

Catalog Number	4T
Manufacturer	Nsi Industries
Description	Mechanical Connector, #14 Awg Conductor Size, #4 Awg Conductor Size, Non-Insulated, Aluminum/Copper Conductor Material, 1 Conductor, +90 °C Operating Temperature, 1.06 In Overall Length, Screw Terminal, 600 V, 0.02 LB/Ea
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Warranty	1 YEAR
----------	--------

Descriptions

Description	414AWG DU RATED LUG
extra long description	NSI 4T Dual Rated Lug 4-14 AWG
Features	1 Port Aluminum Lug 4-14 AWG Aluminum Single Lugs are versatile and reuseable set screw connectors made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Temperature Rating 90 degrees C. Rated 600 volts (2000V max. per UL486B). UL 486A/B Listed. .

Manufacturer Information

GTIN	00662381001016
UPC	662381001016

Packaging

Carton	1
Package	100
Weight Per each	0.02