



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5021M 105-130V 1200W, Mov, Delayed Response, Turnlock

Nsi Industries

Catalog Number	5021M
Manufacturer	Nsi Industries
Description	Delayed Response Utility, 105 to 130 V Ac, 1200 W, 3.187 In Width, 2.187 In Height, Lexan Housing Material, Gray, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Twist Lock Mount, 0.2 LB/Ea
Weight per unit	0.2000 (lbs/each)
Product Category	Lighting Photocells

Features

supply voltage	105-130 VAC
Timing Range	2 Minutes

Dimensions and Weight

Size	H=2.187 - W=3.187
------	-------------------

Descriptions

Description	105-130V 1200W, MOV, DELAYED RESPONSE, TURNLOCK
extra long description	TORK 5021M TurnLock Utility 120V .5

Manufacturer Information

GTIN	00786261610157
UPC	786261610157

Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	Delayed Response Utility Grade

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Street-Highway Lighting
Enclosure	Lexan Housing
environmental conditions	-40 to + 140 F
Frequency Rating	50-60 Hz
Mounting	TWIST LOCK
Operating Temperature	-40 to + 140 F
standard	cULus