



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5021M 105-130V 1200W, Mov, Delayed Response, Turnlock

Nsi Industries

Catalog Number	5021M
Manufacturer	Nsi Industries
Description	Delayed Response Utility, 105 to 130 V Ac, 1200 W, 3.187 In Width, 2.187 In Height, Lexan Housing Material, Gray, Cadmium Coated CDS Photocell Sensor, -40 °F Operating Temperature, +140 °F Operating Temperature, Twist Lock Mount, 0.2 LB/Ea
Weight per unit	0.2000 (lbs/each)
Product Category	Lighting Photocells

Features

supply voltage	105-130 VAC
Timing Range	2 Minutes

Dimensions and Weight

Size	H=2.187 - W=3.187
------	-------------------

Descriptions

Description	105-130V 1200W, MOV, DELAYED RESPONSE, TURNLOCK
-------------	---

Manufacturer Information

GTIN	00786261610157
UPC	786261610157

Taxonomies, Classifications, and Categories

Category Description	Commercial dimmers, motion sensors, & photo cells
Type	Delayed Response Utility Grade

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Street-Highway Lighting
Enclosure	Lexan Housing
environmental conditions	-40 to + 140 F
Frequency Rating	50-60 Hz
Mounting	TWIST LOCK
Operating Temperature standard	-40 to + 140 F cULus